

Pneumatic chipping hammer set CP7111HK

plus 5 different chisels



Application:

Chipping hammer suitable for a wide variety of applications and accessories.

Execution:

- with a sturdy metal housing

Advantage:

- Handy, light and ergonomic
- Easily replaced bracket for quick replacement

Delivery:

incl. line oilers, plug-in nipple, retaining spring and 5 different chisels for metal finishing and bodywork.



Art. no.	75032 150
Brand	CP
Manufacturer Part Number	8941171111
Model	CP7111HK
Impact energy	7.2
Max. impact rate	3000 rpm
Air consumption	11.8 l/s
Tool holding device	10,2 mm HEX
Connection thread	1/4 inch
Inner hose diameter	10 mm
Sound-pressure level	100
Weight	1.6 kg
Gross Weight	3.215 kg
Product Group	752

EAN

0015451590857