




HX-SCE

TE Internal #: F54891-000

HX-SCE, Printable Tubing, Ladder Printable Tubing Type, Low Fire Hazard Printable Tubing Grade, 2:1 Printable Tubing Shrink Ratio, Yellow, 1 Prescore

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > HX-SCE LOW FIRE HAZARD SLEEVES



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Low Fire Hazard**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **Yellow**

Number of Prescores: **1**

[All HX-SCE LOW FIRE HAZARD SLEEVES \(48\)](#)

Features

Product Type Features

| | |
|------------------------|-----------------|
| Printable Tubing Type | Ladder |
| Printable Tubing Grade | Low Fire Hazard |

Body Features

| | |
|-------------------------------|--------|
| Printable Tubing Shrink Ratio | 2:1 |
| Primary Product Color | Yellow |
| Markers per Sleeve | 2 |

Dimensions

| | |
|---------------------------------|-----------------------------|
| Product Length | 25 mm[1 in] |
| Supplied Inner Diameter | 19 mm[.73 in] |
| Recovered Inside Diameter | 9.5 mm[.375 in] |
| Compatible Cable Diameter Range | 10.1 – 16.2 mm[.4 – .64 in] |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

| | |
|--------------------|--|
| Recommended Ribbon | See TE Document 411-121005 the Printer Product Ribbon Matrix |
|--------------------|--|



Printer/Label Features

| | |
|---------------------|--|
| Recommended Printer | See TE Document 411-121005 the Printer Product Ribbon Matrix |
| Printer Technology | Thermal Transfer |
| Number of Prescores | 1 |

Packaging Features

| | |
|--------------------|------|
| Packaging Quantity | 1000 |
|--------------------|------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # CP8122-000
T6112DS-PRINTER




TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series | HX-SCE



Printable Tubing(49)


Customers Also Bought



TE Part #154665-000
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #2-1755142-0
7022WCITV=RLY,STD,OFF,2P,96V,15S, I,T,V



TE Part #404673-000
342A112-100-0



TE Part #6-1393809-5
Signal Relays: 5 amp, Monostable DC



TE Part #1393819-4
CRADLE N RELAY V23162



TE Part #1415060-1
Force Guided Power Relay, DIN-rail



TE Part #ZPF00000000112132
UIC558 PLUG - MALE - 13 OR 18 PINS



TE Part #176819-000
B-150-11



Documents

Product Drawings

[HX-SCE-1K-19.0-50-S1-4](#)

English

Datasheets & Catalog Pages

[Technical Datasheet for HX-SCE Heat Shrink Marker Sleeves](#)

English

[Cable Identification Product Shelf Life](#)

English

[IDENTIFICATION SELECTION GUIDE](#)

English

Product Specifications

[HX - LFH Heat Shrink Sleeving](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English