

Short taper flange

Made of cast iron



Application:

For retroactive fastening of lathe chucks.

Execution:

- Ready-machined on machine side and chuck side, spindle heads with bayonet fastening in accordance with DIN ISO 702-3 (formerly DIN 55027).

Art. no.	22505 115
Brand	BISON
Manufacturer Part Number	358230161500
Flange diameter	250 mm
Taper shank size	6
Pitch circle diameter	224 mm
Taper diameter	106.39 mm
Drill hole	103 mm
Ratio	200 mm
Number of bolts	6/4 pieces
Flange thickness	28 mm
Thread dimension	M12 x 6
Gross Weight	7.500 kg
Product Group	221

