

## Air hydraulic single piston pumps

For single-acting cylinders



### Execution:

- For single-acting cylinders.
- For hand or foot actuation with built-in 3-way air valve that automatically holds the load in the event of air pressure loss. No idling as the pump only works when oil delivery is required. When the set pressure is reached, the pump switches off automatically. The pump can be connected to any compressed air network with a minimum air delivery rate of 250 l/min.
- With silencer
- Rotating oil connection.
- Air connection, 1/4 inch 18 NPT.
- With pressure limiting valve.
- With maximum operating pressure of 700 bar.

### Delivery:

1x ENERPAC air hydraulic single piston pump PA-133 700 bar.



<b>Art. no.</b>	<b>29703 030</b>
<b>Brand</b>	ENERPAC
<b>Manufacturer Part Number</b>	PATG1102N
<b>Model</b>	PATG-1102 N
<b>Usable oil volume</b>	2081 cm <sup>3</sup>
<b>Min./max. feed quantity</b>	1.00-0.16 l/min
<b>Min. air pressure</b>	4.1 bar
<b>Max. air pressure</b>	8.6 bar
<b>Connection thread</b>	NPTF 3/8 inch - 18
<b>Gross Weight</b>	7.662 kg
<b>Product Group</b>	258