

P/N: TG54-2

Copyright

© 2023, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: TG54-2
 Commit: 92629
 Language: en-US
 Modified: 2023-06-28
 Formatted: 2023-07-13

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
Part number	TG54-2
Part name	20:1 Spot IR Thermometer
<p>The FLIR TG54-2 Spot IR Thermometer provides non-contact surface temperature readings so you can quickly and easily take measurements in places that are out of reach. Providing a distance-to-spot ratio of up to 20:1, the FLIR TG54-2 can measure small targets from a safe distance. New mode options give you control to view your current reading and the last two temperature readings simultaneously. The FLIR TG54-2 has a color screen that makes it easy to navigate and select settings, plus adds visibility and efficiency to the advanced feature set. The FLIR TG54-2 is your go-to, pocket-sized device for efficient temperature measurement.</p>	
<p>Measure high and low:</p> <ul style="list-style-type: none"> • Easily take measurements in hard-to-reach spots at a distance. • Take non-contact surface temperature measurements with an infrared sensor. • 20:1 spot ratio to measure small targets from a safe distance. • Easily identify measurement locations with built-in laser targeting. 	
<p>Simple to use:</p> <ul style="list-style-type: none"> • Color display, easy to navigate. • Graphical menu structure allows easy access to settings. • Easy emissivity selection with predetermined levels and custom adjustment. • Visual high and low alarms. 	
<p>Convenient and rugged design:</p> <ul style="list-style-type: none"> • Portable, compact size. • Rugged, industrial IP65 design that can withstand a 3 m drop. • Bright worklight to help you see your target in poor lighting conditions. 	
Spot infrared (IR) thermometer	
IR temperature range	-30°C to +850°C (-22°F to +1562°F)
Basic accuracy	0°C to 100°C (32°F to 212°F): ±1.0°C (±1.8°F)
Emissivity	0.01 to 1.00 with 5 presets
Distance to spot	20:1
Field of view angle	0.04°
Measurement resolution	0.1°C (0.1°F)
IR temperature response time	250 ms
Spectral response	8 μm to 14 μm



FLIR TG54-2: 20:1 Spot IR Thermometer

P/N: TG54-2

© 2023, FLIR Systems, Inc.

#TG54-2; r. 92629; en-US

Spot infrared (IR) thermometer	
Max/Min	Min/Max/Avg/Dif Avg is from last 20 readings
Alarms	High/low alarms with programmable set points
Alarm alert	HI or LO will flash on the display

Laser	
Laser type	Single class II laser (red; visible light)
Laser power	≤ 1 mW, Class II
Laser alignment	Single point laser to upper edge of measurement

Power source	
Battery	9V alkaline battery (included)
Continuous Run Time	8 hours maximum continuous temperature measurements
Auto Power Off	5 or 15 seconds (selectable)
Battery documents	For documents like MSDS and UN38.3 test reports/summaries, see: https://support.flir.com/resources/msds

General	
Display	1.57" Color EBTN
Datalogging	Manual and automatic data logger
Memory	2 × 99 sets data storage
Scanning mode	Yes
Warranty	Limited 3-Year Warranty https://www.flir.com/testwarranty
Drop test	3 m (9.8 ft.)
IP rating	IP65
Worklight	Yes
Certifications	CE, UKCA, RCM, WEEE and FDA
Declaration of conformity	See: https://support.flir.com/resources/DoC

Physical data	
Weight	292 g (10.3 oz.)
Dimensions (L × W × H)	192 mm × 94 mm × 64 mm (7.5 in. × 3.7 in. × 2.5 in.)

Shipping information	
Packaging type	Retail gift box
Packaging contents	<ul style="list-style-type: none">Spot IR Thermometer9V batteryQuick Start GuideStorage Pouch
Packaging weight:	0.683 kg (1.5 lb.)
Packaging dimensions (L × W × H)	28.5 cm × 15 cm × 7.5 cm (11.2 in. × 5.9 in. × 2.95 in.)
UPC	793950402542
EAN	0793950402542



FLIR TG54-2: 20:1 Spot IR Thermometer

P/N: TG54-2

© 2023, FLIR Systems, Inc.

#TG54-2; r. 92629; en-US

Shipping information	
Country of origin	China
Tariff code / ECCN	9025198060 / 3A992a

Technical support	
Website	http://support.flir.com

