




COMPONENT FOR ENCLOSURE, 22MM LAMP
HOLDER WITH INTEGRATED LED 24V AC/DC RATED
VOLTAGE 24V AC/DC SCREW TERMINAL WHITE

Figure similar

Product designation		lampholder
Contact block/ lampholder:		
Mounting type		integrated
Number of lampholders		1
General technical data:		
Product function		
• positive opening		No
Product component		
• diode		Yes
• lamp transformer		No
• Light source		Yes
• series resistor		No
Insulation voltage		
• Rated value	V	250
Type of voltage		
• of the operating voltage		AC/DC
Degree of pollution		class 3
Surge voltage resistance Rated value	kV	4
Protection class IP		
• of the enclosure		IP40
• of the terminal		IP20
Equipment marking		
• acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		H
• acc. to DIN EN 61346-2		P

• acc. to DIN EN 81346-2		P
Operating voltage		
• with AC		
— at 50 Hz Rated value	V	21.6 ... 26.4
— at 60 Hz Rated value	V	21.6 ... 26.4
• for DC Rated value		
— maximum	V	26.4
— minimum	V	21.6
Operating voltage 1		
• with AC		
— at 50 Hz Rated value	V	24
— at 60 Hz Rated value	V	24
• for DC Rated value	V	24

Supply voltage:

Type of voltage of the supply voltage		
• of the light source		AC/DC
Supply voltage 1 of the light source with AC		
• at 50 Hz Rated value	V	24
• at 60 Hz Rated value	V	24
Supply voltage 1 of the light source for DC		
• Rated value	V	24

Auxiliary circuit:

Number of NC contacts		
• for auxiliary contacts		0
Number of NO contacts		
• for auxiliary contacts		0
Number of CO contacts		
• for auxiliary contacts		0

Connections/ Terminals:

Type of electrical connection		screw-type terminals
Type of connectable conductor cross-section		
• for auxiliary contacts		
— solid		2x (1.0 ... 1.5 mm ²)
— solid with core end processing		2x (0.5 ... 0.75 mm ²)
— finely stranded with core end processing		2x (0.5 ... 1.5 mm ²)
• for AWG conductors for auxiliary contacts		2x (18 ... 14)
Tightening torque		
• for auxiliary contacts with screw-type terminals	N·m	0.8

Lamp:

Type of light source		LED
-----------------------------	--	-----

Color of the light source	white
---------------------------	-------

Ambient conditions:

Ambient temperature		
• during operation	°C	-25 ... +70
• during storage	°C	-25 ... +80

Installation/ mounting/ dimensions:

Mounting type		floor mounting
Height	mm	49
Width	mm	10
Depth	mm	28

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other
 CCC	 EG-Konf.	Special Test Certificate	Environmental Confirmations

other

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB34201PE>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB34201PE/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB34201PE&lang=en



last modified:

09.03.2015