



Raychem | Raychem AS85049

TE Internal #: CW2822-000

Raychem AS85049, Screened Backshells & Adapters, 303 Stainless Steel, Cable-to-Cable, Passivated (SAE AMS-QQ-P-35 or MIL-S-5002), M85049 / None

[View on TE.com >](#)

Connectors > Connector Backshells & Adapters > Screened Backshells & Adapters



Backshell Material: **303 Stainless Steel**

Connector System: **Cable-to-Cable**

Adapter Plating Material: **Passivated (SAE AMS-QQ-P-35 or MIL-S-5002)**

Termination Device Type: **M85049, None**

Sealable: **Yes**

Features

Product Type Features

| | |
|-------------------------|----------------|
| Connector System | Cable-to-Cable |
| Termination Device Type | M85049, None |
| Sealable | Yes |

Body Features

| | |
|--------------------------|--|
| Backshell Material | 303 Stainless Steel |
| Adapter Plating Material | Passivated (SAE AMS-QQ-P-35 or MIL-S-5002) |

Industry Standards

| | |
|---------------------------------------|--------------|
| Connector Detail Specification Number | M85049/128-1 |
|---------------------------------------|--------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |



| | |
|---------------------------|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Also in the Series | Raychem AS85049



Backshell Accessories(1)




Screened Backshells & Adapters(137)




Unscreened Backshells & Adapters (267)

Customers Also Bought



TE Part #165938-000
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #158631-000
44AM1131-20-MST3-9CS2275



TE Part #1825619-1
BT1440004=Boot,Toggle



TE Part #127429-000
SO63-5-9030



TE Part #346108-000
S02-13-R



TE Part #251379-000
SO63-3-55-24-90




TE Part #094469-000
55A1124-22-9/96-9CS2275



TE Part #349711-000
55A1822-20-9/96-9CS2275



TE Part #084577-000
SO63-3-55-26-90



TE Part #YDTS32Z09RV0010000
CAP ASSEMBLY

Documents

Product Drawings

[R85049/128-1](#)

English

Datasheets & Catalog Pages

[AS85049 Adapters and Band Straps](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English