

Safety data sheet according to 1907/2006/EC, Article 31

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML
- **Article number:** 440.0001540-0001640.046
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Sector of Use**
 - SU21 Consumer uses: Private households / general public / consumers
 - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC9a Coatings and paints, thinners, paint removers
- **Process category**
 - PROC7 Industrial spraying
 - PROC11 Non industrial spraying
- **Application of the substance / the mixture** Spray varnish
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI B.V.
Wolfraamweg 2
NL-8471 XC Wolvega
Nederland
Tel : +31 (0)561 694400
Fax: +31 (0)561 694411
e-mail: info@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:** +31 (0)561-694400 (09:00h - 17:00h)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



GHS08 health hazard

STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

Aquatic Chronic 3 H412 Harmful to aquatic life with long lasting effects.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: **PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML**

(Contd. of page 1)

· **Hazard pictograms**

GHS02 GHS07 GHS08

· **Signal word** *Danger*· **Hazard-determining components of labelling:***acetone**Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%)**Hydrocarbons, C9, aromatics*· **Hazard statements***H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.**H319 Causes serious eye irritation.**H336 May cause drowsiness or dizziness.**H373 May cause damage to organs through prolonged or repeated exposure.**H412 Harmful to aquatic life with long lasting effects.*· **Precautionary statements***P101 If medical advice is needed, have product container or label at hand.**P102 Keep out of reach of children.**P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.**P211 Do not spray on an open flame or other ignition source.**P251 Do not pierce or burn, even after use.**P260 Do not breathe spray.**P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.**P501 Dispose of contents / container in accordance with regional regulations.*· **Additional information:***EUH066 Repeated exposure may cause skin dryness or cracking.*· **2.3 Other hazards**· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.* **SECTION 3: Composition/information on ingredients**· **3.2 Chemical characterisation: Mixtures**· **Description:** Mixture of substances listed below with nonhazardous additions.· **Dangerous components:**

CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8 Reg.nr.: 01-2119471330-49	<i>acetone</i> ⚠ Flam. Liq. 2, H225 ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	25-<50%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21	<i>propane</i> ⚠ Flam. Gas 1, H220 Press. Gas C, H280	12.5-<20%
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32	<i>butane</i> ⚠ Flam. Gas 1, H220 Press. Gas C, H280	10-<12.5%

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML

(Contd. of page 2)

CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27	isobutane Flam. Gas 1, H220 Press. Gas C, H280	10-<12.5%
EC number: 919-446-0 Reg.nr.: 01-2119458049-33	Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%) Flam. Liq. 3, H226 STOT RE 1, H372; Asp. Tox. 1, H304 Aquatic Chronic 2, H411 STOT SE 3, H336	5-<10%
EC number: 918-668-5 Reg.nr.: 01-2119455851-35	Hydrocarbons, C9, aromatics Flam. Liq. 3, H226 Asp. Tox. 1, H304 Aquatic Chronic 2, H411 STOT SE 3, H335-H336	2.5-<5%
CAS: 1330-20-7 EINECS: 215-535-7 Index number: 601-022-00-9 Reg.nr.: 01-2119488216-32-xxxx	xylene Flam. Liq. 3, H226 STOT RE 2, H373; Asp. Tox. 1, H304 Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319; STOT SE 3, H335 Aquatic Chronic 3, H412	<2.5%

· **Additional information:**

Note C (Regulation (EC) no. 1272/2008) applies to the component Xylene (mixture) CAS: 1330-20-7.
For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**

· **General information:**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After inhalation:** Supply fresh air; consult doctor in case of complaints.

· **After skin contact:** Generally the product does not irritate the skin.

· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.

· **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

· **5.1 Extinguishing media**

· **Suitable extinguishing agents:**

CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

· **5.2 Special hazards arising from the substance or mixture**

During heating or in case of fire poisonous gases are produced.

· **5.3 Advice for firefighters -**

· **Protective equipment:** Mouth respiratory protective device.

SECTION 6: Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures**

Ensure adequate ventilation

Keep away from ignition sources.

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML

(Contd. of page 3)

Mount respiratory protective device.

Wear protective equipment. Keep unprotected persons away.

· **6.2 Environmental precautions:**

Inform respective authorities in case of seepage into water course or sewage system.

Do not allow to enter sewers/ surface or ground water.

· **6.3 Methods and material for containment and cleaning up:**

Dispose contaminated material as waste according to item 13.

Ensure adequate ventilation.

· **6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.

· **Information about fire - and explosion protection:**

Do not spray onto a naked flame or any incandescent material.

Keep ignition sources away - Do not smoke.

Keep respiratory protective device available.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.

· **7.2 Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:**

Observe official regulations on storing packagings with pressurised containers.

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:** Keep container tightly sealed.

· **Storage class:** 2 B

· **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

67-64-1 acetone

WEL Short-term value: 3620 mg/m³, 1500 ppm

Long-term value: 1210 mg/m³, 500 ppm

106-97-8 butane

WEL Short-term value: 1810 mg/m³, 750 ppm

Long-term value: 1450 mg/m³, 600 ppm

Carc (if more than 0.1% of buta-1.3-diene)

1330-20-7 xylene

WEL Short-term value: 441 mg/m³, 100 ppm

Long-term value: 220 mg/m³, 50 ppm

Sk; BMGV

· **Ingredients with biological limit values:**

1330-20-7 xylene

BMGV 650 mmol/mol creatinine

Medium: urine

Sampling time: post shift

Parameter: methyl hippuric acid

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML

(Contd. of page 4)

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes and skin.

Avoid contact with the eyes.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

Butyl rubber gloves with a thickness of 0.4 mm are resistant to:

Acetone: 480 min

Butyl acetate: 60 min

Ethyl acetate: 170 min

Xylene: 42 min

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Aerosol

Colour: Different according to colouring

· **Odour:** Solvent-like

· **Odour threshold:** Not determined.

· **pH-value:** Not determined.

(Contd. on page 6)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: **PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML**

(Contd. of page 5)

· Change in condition Melting point/freezing point: Initial boiling point and boiling range:	Undetermined. Not applicable, as aerosol.
· Flash point:	<0 °C (<32 °F) Not applicable, as aerosol.
· Flammability (solid, gas):	Not applicable.
· Ignition temperature:	>200 °C (>392 °F)
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Explosion limits: Lower: Upper:	1.5 Vol % 13 Vol %
· Vapour pressure at 20 °C (68 °F):	3,500 hPa (2,625.2 mm Hg)
· Density at 20 °C (68 °F): · Relative density · Vapour density · Evaporation rate	0.74 g/cm ³ (6.18 lbs/gal) Not determined. Not determined. Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity: Dynamic: Kinematic:	Not determined. Not determined.
· Solvent content: Organic solvents: · EU-VOC: · EU-VOC in %: · VOC (EC) 591.7 g/l · VOC-EU%	80.3 % 591.9 g/l 80.30 % --- 80.27 %
· Solids content: · 9.2 Other information	19.7 % No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

GB

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML

(Contd. of page 6)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

67-64-1 acetone

Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	>15,800 mg/kg (rabbit)
Inhalative	LC50 / 4h	76 mg/l (rat)

1330-20-7 xylene

Oral	LD50	3,523 mg/kg (rat)
Dermal	LD50	2,000 mg/kg (rabbit)
Inhalative	LC50 / 4 h	29,000 mg/m ³ (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause drowsiness or dizziness.
- **STOT-repeated exposure**
May cause damage to organs through prolonged or repeated exposure.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:**

67-64-1 acetone

LC50/96h	8,300 mg/l (fish)
EC50/96h	7,200 mg/l (algae)
LC50 / 48 h	8,450 mg/l (crustacean (water flea))

1330-20-7 xylene

EC50 / 48 h	7.4 mg/l (daphnia magna)
LC50 / 96 h	13.5 mg/l (fish)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Harmful to fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.
Harmful to aquatic organisms
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML

(Contd. of page 7)

· **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **European waste catalogue**

08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances
-----------	---

15 01 04	metallic packaging
----------	--------------------

· **Uncleaned packaging:**

· **Recommendation:** Non contaminated packagings may be recycled.

SECTION 14: Transport information

· **14.1 UN-Number**

· **ADR, IMDG, IATA** UN1950

· **14.2 UN proper shipping name**

· **ADR** 1950 AEROSOLS

· **IMDG** AEROSOLS

· **IATA** AEROSOLS, flammable

· **14.3 Transport hazard class(es)**

· **ADR**



· **Class** 2 5F Gases.

· **Label** 2.1

· **IMDG, IATA**



· **Class** 2.1

· **Label** 2.1

· **14.4 Packing group**

· **ADR, IMDG, IATA** not regulated

· **14.5 Environmental hazards:** Not applicable.

· **14.6 Special precautions for user** Warning: Gases.

· **Danger code (Kemler):** -

· **EMS Number:** F-D,S-U

· **Stowage Code** SW1 Protected from sources of heat.

SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.

· **Segregation Code** SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: **PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML**

(Contd. of page 8)

·	subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· Transport/Additional information:	
· ADR	
· Limited quantities (LQ)	1L
· Excepted quantities (EQ)	Code: E0 Not permitted as Excepted Quantity
· Transport category	2
· Tunnel restriction code	D
· IMDG	
· Limited quantities (LQ)	1L
· Excepted quantities (EQ)	Code: E0 Not permitted as Excepted Quantity Code: E0 Not permitted as Excepted Quantity
· UN "Model Regulation":	UN 1950 AEROSOLS, 2.1

SECTION 15: Regulatory information

· 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

- Directive 2012/18/EU
- Named dangerous substances - ANNEX I None of the ingredients is listed.
- Seveso category P3a FLAMMABLE AEROSOLS
- Qualifying quantity (tonnes) for the application of lower-tier requirements 150 t
- Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t
- REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3, 40

· National regulations:

· Other regulations, limitations and prohibitive regulations

· Substances of very high concern (SVHC) according to REACH, Article 57

None of the ingredients is listed.

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H335 May cause respiratory irritation.
- H336 May cause drowsiness or dizziness.
- H372 Causes damage to organs through prolonged or repeated exposure.

(Contd. on page 10)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 06.06.2018

Version number 6

Revision: 23.05.2018

Trade name: PLASTI-KOTE® FAST DRY ENAMEL VARIOUS COLOURS 3UC 100 ML

(Contd. of page 9)

H373 May cause damage to organs through prolonged or repeated exposure.

H411 Toxic to aquatic life with long lasting effects.

H412 Harmful to aquatic life with long lasting effects.

· Abbreviations and acronyms:

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Flam. Gas 1: Flammable gases – Category 1

Aerosol 1: Aerosols – Category 1

Press. Gas C: Gases under pressure – Compressed gas

Flam. Liq. 2: Flammable liquids – Category 2

Flam. Liq. 3: Flammable liquids – Category 3

Acute Tox. 4: Acute toxicity – Category 4

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

STOT RE 1: Specific target organ toxicity (repeated exposure) – Category 1

STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2

Asp. Tox. 1: Aspiration hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

· * Data compared to the previous version altered.