

For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x30) tinned copper conductors, Datalene® insulation, twisted pairs, overall Beldfoil® shield (100% coverage) plus a tinned copper braid (65% coverage), drain wire, UV resistant PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	1	22	7x30	TC - Tinned Copper	.030

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material
Datalene®	FHDPE - Foam High Density Polyethylene

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000
2		Braid	TC - Tinned Copper	65.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Shield Drain Wire Diameter: .030

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Cabling Color Code Chart:

Number	Color
1	White/Orange Stripe
2	Orange/White Stripe
3	Blue/White Stripe

Overall Nominal Diameter: 0.300 in.

Pair

Pair Lay Length & Direction:

Lay Length (in.)
3.000

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +60°C

Non-UL Temperature Rating: 60°C

Bulk Cable Weight: 48 lbs/1000 ft.

Max. Recommended Pulling Tension: 65 lbs.

Min. Bend Radius (Install)/Minor Axis: 3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

CEC/C(UL) Specification: CM

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 10/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

CSA Flame Test: FT1

Plenum/Non-Plenum

Plenum (Y/N): No

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)

.203

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

11.0

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

20.9

Nominal Velocity of Propagation:

VP (%)

78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

14.7

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.8

Nom. Attenuation:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Attenuation (dB/100 ft.)
	1			.5

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

2.7 Amps per conductor @ 25°C

Input/Unfitted Impedance:

3106A Multi-Conductor - EIA Industrial RS-485 PLTC/CM

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Impedance (Ohm)
	1			120

Notes (Overall)

Notes: Oil Resistance: Passes Oil Res II Per UL1277, Table 10.17. For CPE jacketed version order YR46721.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3106A 0101000	1,000 FT	47.000 LB	BLACK	C	#22 FS PR,1#22PVCBRDPVC
3106A 010500	500 FT	25.000 LB	BLACK	C	#22 FS PR,1#22PVCBRDPVC
3106A 0105000	5,000 FT	230.000 LB	BLACK	C N	#22 FS PR,1#22PVCBRDPVC

Notes:

C = CRATE REEL PUT-UP.

N = FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 12-05-2008

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.