

## Twist drill type N with soldered cemented carbide insert 4xD

For universal use up to 1500 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

Universal use in all material groups up to a strength of 1500 N/mm<sup>2</sup>.

### Execution:

- Twist drill with universal standard geometry, soldered cemented carbide insert (K20) and driving lug on the clamp shank

### Advantage:

- Cemented carbide insert, K20, for a long service life
- polished chipping spaces ensure good chip removal
- cost-effective tool for broad range of applications



<b>Art. no.</b>	<b>11160 070</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11160070
<b>Cutting edge diameter</b>	7 mm
<b>Chip flute length</b>	40 mm
<b>Length</b>	80 mm
<b>f steel 1300</b>	0.07 mm/r
<b>DIN</b>	8037
<b>Gross Weight</b>	0.021 kg
<b>Product Group</b>	140

### EAN

4039247029945