

Diamond hand lapping tools

with metal bonding

ORION®

Application:

For the maintenance and re-machining of cemented carbide cutting edges.

Version:

- Highly wear-resistant and suitable for robust applications

Advantage:

- Good grip
- High dimensional stability
- Long service life
- Use of the hand lapping tool increases the service life of the cemented carbide cutting edges



Art. no.	60400 010
Binding	Metal
Length	140 mm
Grain size	64 µm
Lining length x lining width	30 x 8 mm
Number of pieces per packet	1 PCS

EAN-Code

4039247332465