

Modular drilling system TDMX drilling depth 5xD

For universal use up to 1300 N/mm², in diameter range of 16.00-40.00 mm

WIDIA 

Execution:

- Drilling depth 5xD
- Diameter range 16-38 mm

Advantage:

- Front clamping, possible to change the cutting body while clamped
- Up to 3x regrinding possible
- Polished chip grooves for better chip removal
- Types developed for material-specific applications



Art. no.	11228 300
Brand	WIDIA
Manufacturer Part Number	6572149
Suitable for min. cutting diameter	30 mm
Suitable for max. cutting diameter	30.99 mm
Shank diameter	32 mm
Length	266 mm
Cantilever length	206 mm
Effective length	155 mm
Shaft length	60 mm
Suitable for indexable inserts type	0
Max. drilling depth (D)	5xD
Coolant supply	Internal
Tool holding device	Parallel shank with chuck surface ISO 9766
Bore type	Normal bore, Stud hole bore, Cross bore, Slanted exit, Slanted entry
Gross Weight	1.017 kg
Product Group	1XB