



MSR Gold™ FastFit

MSR Gold™ 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

Product data

GeniPubl	
Cap-Base	PGJX50 [PGJX50]
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	Entertainment
Life to 50% Failures (Nom)	750 h
System Description	FastFit

LittPubl	
Color Code	2
Luminous Flux (Min)	41800 lm
Luminous Flux (Nom)	50000 lm
Chromaticity Coordinate X (Nom)	298
Chromaticity Coordinate Y (Nom)	322
Correlated Color Temperature (Nom)	7500 K
Luminous Efficacy (rated) (Nom)	71 lm/W
Color Rendering Index (Nom)	75

ElecPubl	
Power (Nom)	700 W
Lamp Current (Nom)	10.2 A
Ignition Supply Voltage (Min)	198 V

CntrPubl	
Dimmable	Yes

MechPubl	
Cap-Base Information	PGJX50

LDRPubl	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	500 °C

ProductPubl	
Full product code	872790090850300


MSR Gold™ FastFit

Order product name	MSR Gold™ 700/2 FastFit 1CT/8
EAN/UPC - Product	8727900908503
Order code	928106205114
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Material Nr. (12NC)	928106205114
Net Weight (Piece)	0.100 kg

Warnings and Safety

Dimensional drawing





MSR GOLD 700/2 FastFit

Product

MSR Gold™ 700/2 FastFit 1CT/8

Photometric data



XDPB_XDMSR_0001-Spectral power distribution B/W

