

Product characteristics

Inductive sensor

Metal thread M8 x 1

Cable with connector

Sensing range 3 mm; [nfr] non-flush mountable

Electrical data

Electrical design

DC PNP

Operating voltage [V]

10...36 DC

Current consumption [mA]

< 15

Protection class

III

Reverse polarity protection

yes

Outputs

Output function

normally open

Voltage drop [V]

< 2.5

Current rating [mA]

200

Short-circuit protection

pulsed

Overload protection

yes

Switching frequency [Hz]

300

Range

Sensing range [mm]

3

Real sensing range (Sr) [mm]

3 ± 10 %

Operating distance [mm]

0...2.4

Accuracy / deviations

Correction factors

mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3

Hysteresis [% of Sr]

1...15

Switch-point drift [% of Sr]

-10...10

Environment

Ambient temperature [°C]

0...70

Protection

IP 67

Tests / approvals

EMC

EN 60947-5-2

EN 55011:

class B

MTTF [Years]

2819

Mechanical data

Mounting

non-flush mountable

Housing materials

high-grade stainless steel; active face: PBT

Weight [kg]

0.055

Displays / operating elements

Output status indication LED

Red


Electrical connection

Connection

PVC cable / 1.5 m; 3 x 0.14 mm<sup>2</sup>; with M12 connector

**Wiring**

**IE5376 - Inductive sensor - eclass: 27270101 / 27-27-01-01**



Accessories

Accessories (included)

2 lock nuts

Remarks

Pack quantity

[piece]

1