HUBER+SUHNER® DATA SHEET RF TERMINATION: Type 65_BNC-50-0-7/133_N

Rev.: G

Description

Standard Termination, Low Power

Product Configuration

Connector BNC plug (male)

Interface standard IEC 60169-8_MIL-STD-348A/301_CECC 22120

Technical Data Electrical Data

Nominal impedance 50 Ω

Frequency range DC to 1 GHz

Frequency sub range (GHz) DC to 0.3 0.3 to 1 VSWR max. 1.05 1 1

Power rating 1 Watt average power up to 30 °C ambient temperature, linearly derated to 0 Watt at 130 °C

ambient temperature. 2000 Watt peak power

Mechanical Data

Weight 0.016 kg

Environmental Data

2002/95/EC (RoHS) compliant

Material Data

Piece Part Material **Surface Plating**

Centre contact **Brass** Gold Plating (Nickel underplated) Outer contact Brass SUCOPLATE (R) Plating SUCOPLATE (R) Plating Body **Brass**

Insulator PFA / PTFE

Coupling nut SUCOPLATE (R) Plating Brass

Related Documents

Outline drawing On request

Ordering Information

Single packaging 65_BNC-50-0-7/133_NE Bulk 100 pcs packaging 65 BNC-50-0-7/133 NH

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVERI

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only

HUBER+SUHNER – Excellence in Connectivity Solutions

Document: DOC-0000227425 J **Uncontrolled Copy** Issued: 11.11.09 Page 1/1



HUBER+SUHNER AG RF Industrial 9100 Herisau, Switzerland Phone +41 (0)71 353 41 11 +41 (0)71 353 45 90 www.hubersuhner.com