

SIMATIC S7-1200, DIGITAL INPUT, SM 1226, F-DI 16X 24VDC, PROFISAFE, 70 MM WIDTH, UP TO PL E (ISO 13849-1)/ UP TO SIL3 (IEC 61508)



Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> • 24 V DC 	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
from backplane bus 5 V DC, max.	155 mA; Current consumption (SM Bus, 5 V DC): 155 mA
Digital inputs	
<ul style="list-style-type: none"> • from load voltage L+ (without load), max. 	130 mA; 130 mA + 6 mA / input used + any Vs1/Vs2 current used
Power loss	
Power loss, typ.	7 W
Digital inputs	
Number of digital inputs	16; 16 (1oo1) or 8 (1oo2); Note: You can individually assign each pair of inputs "a.x" and "b.x" as a single (1oo2)-channel or as 2 separate (1oo1)-channels
Number of simultaneously controllable inputs	
horizontal installation	
— up to 50 °C, max.	16; 16 inputs at 55 °C horizontal

vertical installation	
— up to 40 °C, max.	16; 16 inputs at 45 °C vertical
Input voltage	
• Type of input voltage	DC
• for signal "0"	-30 V DC to +5 V DC
• for signal "1"	15 V DC to 30 V DC
Input current	
• for signal "0", max. (permissible quiescent current)	0.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.8 / 1.6 / 3.2 / 6.4 / 12.8 ms
Cable length	
• shielded, max.	200 m; Unshielded with input filter time of 1.6 ms to 12.6 ms (With an input delay of 0.8 ms, shielded cables must be used for the digital inputs and the sensor supply)
• unshielded, max.	200 m; Shielded with input filter time of 0.8 ms to 12.6 s (With an input delay of 0.8 ms, shielded cables must be used for the digital inputs and the sensor supply)
Interrupts/diagnostics/status information	
Diagnostics indication LED	
• for status of the inputs	Yes
Standards, approvals, certificates	
CE mark	Yes
cULus	Yes
FM approval	Yes
Highest safety class achievable in safety mode	
• SIL acc. to IEC 61508	SIL 2 (single-channel), SIL 3 (two-channel)
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
• permissible temperature change	5°C to 55°C, 3°C / minute
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
Relative humidity	

• permissible range (without condensation) at 25 °C 95 %

Mechanics/material

Enclosure material (front)

- Plastic

Yes

Dimensions

Width

70 mm

Height

100 mm

Depth

75 mm

Weights

Weight, approx.

250 g

last modified:

24.02.2016