



SIMATIC S7-300, CPU 314 CPU WITH MPI INTERFACE, INTEGRATED 24V DC POWER SUPPLY, 128 KBYTE WORKING MEMORY, MICRO MEMORY CARD NECESSARY

Figure similar

Product type designation	
General information	
Hardware product version	01
Firmware version	V3.3
Engineering with	
<ul style="list-style-type: none"> Programming package 	STEP 7 V5.5 + SP1 or higher or STEP7 V5.2 + SP1 or higher with HSP 218
Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> 24 V DC 	Yes
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
External protection for supply cables (recommendation)	2 A min.
Mains buffering	
<ul style="list-style-type: none"> Mains/voltage failure stored energy time Repeat rate, min. 	5 ms 1 s
Input current	
Current consumption (rated value)	650 mA
Current consumption (in no-load operation), typ.	140 mA
Inrush current, typ.	3.5 A
I^2t	1 A ² ·s
Power losses	
Power loss, typ.	4 W

Memory	
Work memory	
<ul style="list-style-type: none"> • Integrated 	128 kbyte
<ul style="list-style-type: none"> • expandable 	No
<ul style="list-style-type: none"> • Size of retentive memory for retentive data blocks 	64 kbyte
Load memory	
<ul style="list-style-type: none"> • pluggable (MMC) 	Yes
<ul style="list-style-type: none"> • pluggable (MMC), max. 	8 Mbyte
<ul style="list-style-type: none"> • Data management on MMC (after last programming), min. 	10 y
Backup	
<ul style="list-style-type: none"> • present 	Yes; Guaranteed by MMC (maintenance-free)
<ul style="list-style-type: none"> • without battery 	Yes; Program and data
CPU processing times	
for bit operations, typ.	0.06 μ s
for word operations, typ.	0.12 μ s
for fixed point arithmetic, typ.	0.16 μ s
for floating point arithmetic, typ.	0.59 μ s
CPU-blocks	
Number of blocks (total)	1 024; (DBs, FCs, FBs); the maximum number of loadable blocks can be reduced by the MMC used.
DB	
<ul style="list-style-type: none"> • Number, max. 	1 024; Number range: 1 to 16000
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
FB	
<ul style="list-style-type: none"> • Number, max. 	1 024; Number range: 0 to 7999
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
FC	
<ul style="list-style-type: none"> • Number, max. 	1 024; Number range: 0 to 7999
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
OB	
<ul style="list-style-type: none"> • Description 	see instruction list
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
<ul style="list-style-type: none"> • Number of free cycle OBs 	1; OB 1
<ul style="list-style-type: none"> • Number of time alarm OBs 	1; OB 10
<ul style="list-style-type: none"> • Number of delay alarm OBs 	2; OB 20, 21
<ul style="list-style-type: none"> • Number of time interrupt OBs 	4; OB 32, 33, 34, 35
<ul style="list-style-type: none"> • Number of process alarm OBs 	1; OB 40
<ul style="list-style-type: none"> • Number of startup OBs 	1; OB 100
<ul style="list-style-type: none"> • Number of asynchronous error OBs 	4; OB 80, 82, 85, 87

• Number of synchronous error OBs	2; OB 121, 122
Nesting depth	
• per priority class	16
• additional within an error OB	4
Counters, timers and their retentivity	
S7 counter	
• Number	256
Retentivity	
— can be set	Yes
— lower limit	0
— upper limit	255
— preset	Z 0 to Z 7
Counting range	
— lower limit	0
— upper limit	999
IEC counter	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
S7 times	
• Number	256
Retentivity	
— can be set	Yes
— lower limit	0
— upper limit	255
— preset	No retentivity
Time range	
— lower limit	10 ms
— upper limit	9 990 s
IEC timer	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
Data areas and their retentivity	
Total retentive data area	All, max. 64 KB
Flag	
• Number, max.	256 byte
• Retentivity available	Yes; MB 0 to MB 255
• Retentivity preset	MB 0 to MB 15
• Number of clock memories	8; 1 memory byte
Data blocks	

• Number, max.	1 024; Number range: 1 to 16000
• Size, max.	64 kbyte
• Retentivity adjustable	Yes; via non-retain property on DB
• Retentivity preset	Yes
Local data	
• per priority class, max.	32 kbyte; Max. 2 KB per block
Address area	
I/O address area	
• Inputs	1 024 byte
• Outputs	1 024 byte
Process image	
• Inputs	1 024 byte
• Outputs	1 024 byte
• Inputs, adjustable	1 024 byte
• Outputs, adjustable	1 024 byte
• Inputs, default	128 byte
• Outputs, default	128 byte
Digital channels	
• Inputs	1 024
— Inputs, of which central	1 024
• Outputs	1 024
— Outputs, of which central	1 024
Analog channels	
• Inputs	256
— Inputs, of which central	256
• Outputs	256
— Outputs, of which central	256
Hardware configuration	
Expansion devices, max.	3
Number of DP masters	
• Integrated	0
• Via CP	4
Number of operable FMs and CPs (recommended)	
• FM	8
• CP, point-to-point	8
• CP, LAN	10
Rack	
• Racks, max.	4
• Modules per rack, max.	8
Time of day	

Clock	
• Hardware clock (real-time clock)	Yes
• battery-backed and synchronizable	Yes
• Deviation per day, max.	10 s; Typ.: 2 s
• Backup time	6 wk; At 40 °C ambient temperature
• Behavior of the clock following POWER-ON	Clock continues running after POWER OFF
• Behavior of the clock following expiry of backup period	Clock continues to run with the time at which the power failure occurred
Operating hours counter	
• Number	1
• Number/Number range	0
• Range of values	0 to 2 ³¹ hours (when using SFC 101)
• Granularity	1 hour
• retentive	Yes; Must be restarted at each restart
Clock synchronization	
• supported	Yes
• to MPI, master	Yes
• to MPI, slave	Yes
• in AS, master	Yes
• in AS, slave	No
Digital inputs	
Number of digital inputs	0
Digital outputs	
Number of digital outputs	0
Analog inputs	
Number of analog inputs	0
Analog outputs	
Number of analog outputs	0
Interfaces	
Number of USB interfaces	0
Number of 20 mA interfaces (TTY)	0
Number of RS 232 interfaces	0
Number of RS 422 interfaces	0
Number of parallel interfaces	0
Number of other interfaces	0
1st interface	
Interface type	Integrated RS 485 interface
Physics	RS 485
Isolated	No
Power supply to interface (15 to 30 V DC), max.	200 mA

Functionality	
• MPI	Yes
• DP master	No
• DP slave	No
• Point-to-point connection	No
MPI	
• Transmission rate, max.	187.5 kbit/s
Services	
— PG/OP communication	Yes
— Routing	No
— Global data communication	Yes
— S7 basic communication	Yes
— S7 communication	Yes; Only server, configured on one side
— S7 communication, as client	No
— S7 communication, as server	Yes
Communication functions	
PG/OP communication	Yes
Data record routing	No
Global data communication	
• supported	Yes
• Number of GD loops, max.	8
• Number of GD packets, max.	8
• Number of GD packets, transmitter, max.	8
• Number of GD packets, receiver, max.	8
• Size of GD packets, max.	22 byte
• Size of GD packet (of which consistent), max.	22 byte
S7 basic communication	
• supported	Yes
• User data per job, max.	76 byte
• User data per job (of which consistent), max.	76 byte; 76 bytes (with X_SEND or X_RCV); 64 bytes (with X_PUT or X_GET as server)
S7 communication	
• supported	Yes
• as server	Yes
• As client	Yes; Via CP and loadable FB
• User data per job, max.	180 byte; With PUT/GET
• User data per job (of which consistent), max.	240 byte; as server
S5-compatible communication	
• supported	Yes; via CP and loadable FC
Number of connections	
• overall	12

• usable for PG communication	11
— reserved for PG communication	1
— Adjustable for PG communication, min.	1
— Adjustable for PG communication, max.	11
• usable for OP communication	11
— reserved for OP communication	1
— adjustable for OP communication, min.	1
— adjustable for OP communication, max.	11
• usable for S7 basic communication	8
— Reserved for S7 basic communication	0
— adjustable for S7 basic communication, min.	0
— adjustable for S7 basic communication, max.	8

S7 message functions

Number of login stations for message functions, max.	12; Depending on the configured connections for PG/OP and S7 basic communication
Process diagnostic messages	Yes
simultaneously active Alarm-S blocks, max.	300

Test commissioning functions

Status block	Yes; Up to 2 simultaneously
Single step	Yes
Number of breakpoints	4

Status/control

• Status/control variable	Yes
• Variables	Inputs, outputs, memory bits, DB, times, counters
• Number of variables, max.	30
— of which status variables, max.	30
— of which control variables, max.	14

Forcing

• Forcing	Yes
• Force, variables	Inputs, outputs
• Number of variables, max.	10

Diagnostic buffer

• present	Yes
• Number of entries, max.	500
— can be set	No
— Of which powerfail-proof	100; Only the last 100 entries are retained
• Number of entries readable in RUN, max.	499
— can be set	Yes; From 10 to 499
— preset	10

Service data	
• Can be read out	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	60 °C
Configuration	
Configuration software	
• STEP 7	Yes; V5.2 SP1 or higher with HW update
programming	
• Command set	see instruction list
• Nesting levels	8
• System functions (SFC)	see instruction list
• System function blocks (SFB)	see instruction list
Programming language	
— LAD	Yes
— FBD	Yes
— STL	Yes
— SCL	Yes
— CFC	Yes
— GRAPH	Yes
— HiGraph®	Yes
Know-how protection	
• User program protection/password protection	Yes
• Block encryption	Yes; With S7 block Privacy
Dimensions	
Width	40 mm
Height	125 mm
Depth	130 mm
Weights	
Weight, approx.	280 g
last modified:	12.03.2015