


Fig. 750 Series  
Delivered without miniature WSB markers

This interface allows the connection of any device which is equipped with a RS-232 C serial interface.

The shield (screen) is directly connected to the carrier rail.

The interface works in accordance with the TIA/EIA-232-F, CCITT V.28/DIN 66259-1 standard.



The connected device may directly communicate over the fieldbus coupler with the control unit. The active communication channel works independently of the higher-level fieldbus system and allows full duplex operation up to 19200baud.

The RS-232 C interface guarantees high interference immunity because of the electrically isolated signals.

Description	Item No.	Pack. Unit
RS-232 C/ 9600/ N/ 8/ 1	750-650	1
RS-232 C/ 9600/ N/ 8/ 1/ 5 Byte	750-650/000-001	1
RS-232 C/ 9600/ E/ 7/ 2	750-650/000-002	1
RS-232 C/ 4800/ E/ 7/ 1	750-650/000-004	1
RS-232 C/ 9600/ E/ 8/ 1	750-650/000-006	1
RS-232 C/ 2400/ E/ 8/ 1	750-650/000-009	1
RS-232 C/ 19200/ N/ 8/ 1	750-650/000-010	1
RS-232 C/ 19200/ E/ 8/ 1	750-650/000-011	1
RS-232 C/ 2400/ N/ 8/ 1	750-650/000-012	1
RS-232 C/ 4800/ E/ 7/ 2	750-650/000-013	1
RS-232 C/ 4800/ E/ 8/ 1	750-650/000-015	1
RS-232 C/ Configurable	750-650/003-000	1
RS-232 C Interface (without connector)	753-650	1
RS-232 C/ Configurable (without connector)	753-650/003-000	1

Technical Data	
Transmission channels	1 Tx/D / 1 Rx/D, full duplex
Baud rate	9600 baud (factory preset)
	1200 ... 19200 baud
Bit skew	< 3 %
RS-232 line length (max.)	15 m
Buffer	128 bytes in/16 bytes out
Max. current consumption (internal)	55 mA
Power supply	via system voltage DC/DC
Isolation	500 V system/supply
Internal bit width	1 x 24 bits in/out (3 bytes user data)
	1 x 8 bits control/status
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> / AWG 28 ... 14
Strip lengths, 750/753 Series	8 ... 9 mm / 0.33 in
	9 ... 10 mm / 0.37 in
Width	12 mm
Weight	51.5 g
EMC immunity of interference	acc. to EN 61000-6-2, marine applications
EMC emission of interference	acc. to EN 61000-6-4, marine applications

Approvals	
Conformity marking	CE
Korea Certification	☐ <sup>1)</sup>
Marine applications (versions upon request)	ABS, BV, DNV, GL, KR, LR, NKK, PRS, RINA
UL 508	
ANSI/ISA 12.12.01	Class I, Div. 2, Grp. ABCD, T4
TÜV 07 ATEX 554086 X	I M2 Ex d I Mb, II 3 G Ex nA IIC T4 Gc, II 3 D Ex tc IIIC T135°C Dc
Permissible ambient temperature	0 °C ... +60 °C
IECEx TUN 09.0001 X	Ex d I Mb, Ex nA IIC T4 Gc, Ex tc IIIC T135°C Dc
Permissible ambient temperature	0 °C ... +60 °C

<sup>1)</sup> Does not apply to 750-650/003-000

Accessories	Item No.	Pack. Unit
753 Series Connectors	753-110	25
Coding elements	753-150	100
<b>Miniature WSB Quick marking system</b>		
plain	248-501	5
with marking	see Section 11	