

Digital display units

for Mitutoyo length measuring system Linear Scale

Mitutoyo

Application:

Multi-function display for connection to linear scales. Ideal for retrofitting to processing machines such as turning or milling machines.

Execution:

- Robust housing
- 8-digit display plus prefix (-)
- Robust membrane keyboard
- Reading 0.005/0.001 mm
- Reading 0.0001/0.0005 inch

Advantage:

- Large number of functions, e.g. Zero setting, preset, diameter display, half display value, switch between mm/inch, etc.
- Properties, e.g. Feed speed display, taper machining function etc.
- Calculation functions, e.g. +, -, ×, ÷, Cos, Sin, Tan, ARC, √, π



Art. no.	39979 010
Brand	MITUTOYO
Manufacturer Part Number	174-183D
Model	KA-212
Number of axes	2
Min./max. operating temperature	0 to 45 °C
Width	167 mm
Functions	Preset function, With mm / inch switching
Weight	1.25 kg
Height	260 mm
Height x width x depth	260 x 167 x 80 mm
Depth	80 mm
Digit increment, electronic display unit	0,005 μ, 0,001 μ
Gross Weight	1.250 kg
Product Group	3MD

EAN

4946368693538