

Mobile collection tray

With perforated panel

Application:

mobile, secure and easy filling of oils etc. at various points of consumption from 60-l and 200-l drums.

Execution:

- 3-mm thick welded sheet steel structure
- Stable, zinc-plated sheet steel panel with square perforation (10x10 mm), 38 mm hole intervals, for free positioning of tool holders
- hot-dip galvanised sliding handles
- with galvanised grating (carrying capacity 1000 kg/m²)
- 2 steering rollers and 2 fixed castors



Art. no.	50060 564
Collection volume	215 l
Max. number of 200-litre containers	2
Length	1280 mm
Width	800 mm
Height	2015 mm
For liquids hazardous to water GHS 1-4	Yes
For flammable liquids GHS 1-3	Yes
Declaration of conformity in acc. with StawaR	Yes
With grating	Yes
Material	Sheet steel
Surface	Lacquered
Colour	Reseda green RAL 6011
Gross Weight	110.000 kg
Product Group	5A1

EAN

4052462061248