

JETCO torque screwdrivers

with dial gauge, trailing pointer and calibration certificate

Execution:

- large, reflection-free scale window allows for accurate and fast reading
- robust design with strengthened scale housing
- ergonomic handle
- measurements can be taken regardless of force application point
- for right- and left-handed operation, with rigid square output

Advantage:

- simple, fast handling

Delivery:

in a rugged plastic case



Art. no.	52245 330
Min. torque	20 Nm
Max. torque	100 Nm
Min./max. torque	20-100 Nm
Scale value torque	2 Nm
Tip size	1/2 inch
Length	559 mm
Error limit (%)	4 %
Calibration certificate	Yes
Gross Weight	2.050 kg
Product Group	531

EAN

4018754284900