



MSD

MSD 250/2 30H 1CT/4

These single ended, compact lamps enable optimal light collection and accurate beam control, while they also provide true daylight color temperatures – all to create great stage brightness and vivid entertainment. And since they offer long lifetime usage they help minimize the cost of ownership via fewer lamp replacements and fewer maintenance man hour costs.

Product data


General Information	
Cap-Base	GY9.5 [GY9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Main Application	Studio/Disco
Life to 50% Failures (Nom)	3000 h
System Description	-
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux (Min)	16000 lm
Luminous Flux (Nom)	18000 lm
Chromaticity Coordinate X (Nom)	289
Chromaticity Coordinate Y (Nom)	305
Correlated Color Temperature (Nom)	8100 K
Luminous Efficacy (rated) (Nom)	72 lm/W
Color Rendering Index (Nom)	70
Operating and Electrical	
Power (Nom)	250 W
Lamp Current (Nom)	3 A
Ignition Supply Voltage (Min)	207 V

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap-Base Information	-
Luminaire Design Requirements	
Bulb Temperature (Max)	500 °C
Pinch Temperature (Max)	350 °C
Product Data	
Full product code	871829122806600
Order product name	MSD 250/2 30H 1CT/4
EAN/UPC - Product	8718291228066
Order code	928099005115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928099005115
Net Weight (Piece)	0.030 kg

MSD

Warnings and Safety

Dimensional drawing



MSD 250/2 30H

Product

MSD 250/2 30H ICT/4

Photometric data

