

SDJC clamp holder with internal cooling, positive

for longitudinal and copy turning with DC indexable insert

ATORN[®]

Application

for longitudinal and copy turning with DC indexable insert, 55°

Version

- precision-manufactured steel support with high-performance internal cooling system, nickel-plated, hardened, type D, working angle 93°, tip angle 55°, clearance angle 7°

Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable work
- streamlined geometry, optimised for contour lathe work
- positive body geometry ensures low cutting forces
- excellent surface quality for medium infeed and finishing



Art. no.	17835 705
ISO name	SDJC R/L 1616 H11 IK G1/8
Shaft height	16 mm
Shank width	16 mm
Length	100 mm
Length of head	20 mm
Programming size	20 mm
Suitable for indexable inserts	DC.. 11T3..
Tool design	Left
DIN	4983

EAN-Code

4050293566390