

Pneumatic straight grinder SRD 3-55/2

60 watt



Application:

For fine grinding, milling and engraving work.

Execution:

- Environmentally friendly owing to central air discharge
- Air discharge to the rear

Advantage:

- Handy ergonomics for effortless grinding
- Very light and handy - extremely slim design.

Delivery:

Includes Collet chuck ZG 5/3 mm, collet chuck spanner 6 + 8 and hose unit; in box



Art. no.	75036 035
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150000925
Model	SRD 3-55/2
Valve design	Rotary valve
Max. idle speed	55000 rpm
Power output	60 W
Air consumption	170 l/min
Connection thread	M16
Inner hose diameter	4.5 mm
Length	151 mm
Diameter of housing	15.5 mm
Max. clamping diameter	3 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	8 mm
Max. HM rotating milling cutter diameter	6 mm
Weight	0.09 kg
Gross Weight	0.814 kg
Product Group	748