

Drehmagnete
D, E und UD
Technische Beschreibung/
Vorzugstypen

Rotary Solenoids
D, E and UD
Technical description/
Preferred types

Ident. Nr. Ident. No.	Bestell-Bezeichnung ¹⁾ Order Code ¹⁾
51407	D24 BOR F DS 9420 24 V DC 100 % ED
51545	D29 BOR F DS 9420 24 V DC 100 % ED
51649	D34 BOR F DS 9420 24 V DC 100 % ED
51672	D39 BOR F DS 9420 24 V DC 100 % ED
61026	D54 BOR F 24 V DC 100 % ED
61027	D59 BOR F DS 9420 24 V DC 100 % ED
12251	D64 BOR F DS 9420 24 V DC 100 % ED
18054	D69 BOR F DS 9420 24 V DC 100 % ED
18854	D74 BOR F 24 V DC 100 % ED
11387	D79 BOR F DS 9420 24 V DC 100 % ED
90126	E59 BOR F DS 9420 24 V DC 100 % ED

Die obenstehenden Drehmagnete werden als Vorzugstypen lagermäßig geführt, damit Sie einen schnellen und preisgünstigen Zugriff für Ihre Versuche haben. Die Vorzugstypen sind in kleinen Stückzahlen (Zwischenverkauf vorbehalten) innerhalb einer Woche lieferbar. Sie sind ausgelegt für 24 V DC und 100 % ED.

Bei Verwendung einer verstellbaren Spannungsquelle kann der Magnet über die Nennspannung hinaus betrieben werden, um die für die Betätigung erforderliche Kraft zu erreichen.

Beachten Sie hierbei bitte, dass bei längerem Betrieb an erhöhter Betriebsspannung diese Magnete überhitzt werden, wenn nicht ausreichende Pausen bei einer max. Spieldauer (Einschaltzeit + Ausschaltzeit) von 5 Minuten eingehalten werden.

Die Berechnung hierzu ersehen Sie bitte aus den Seiten 20-21.

Zur Festlegung der für Ihren Anwendungsfall erforderlichen Kraft ist der Spulenstrom zu messen. Die genaue Festlegung der Einschaltdauer erfolgt in unserer Entwicklungsabteilung; geben Sie uns bitte hierzu den Magnetspulenstrom an.

Drehmagnete können auf Anfrage auch mit 2 RS-Lagern montiert werden.

Dabei ist zu beachten, dass das Anfangsdrehmoment M_A je nach Magnetgröße ca. 10 % geringer ist, als in den Datenblättern angegeben. Magnete in der Ausführung DS 9420 und Drehwinkel 95° sollten nicht mit 2 RS-Lagern montiert werden.

Hinweis: Bestellformel siehe Seite 147.

¹⁾ DS 9420 beinhaltet eine weich einstellbare Rückholfeder.

The rotary solenoids listed in the table are preferred types and are always in stock, enabling you to have them delivered quickly and at a competitive price for your tests.

The preferred types can be delivered within a week (in small numbers) subject to current order level. They are designed to operate at 24 V DC and 100 % ED.

If an adjustable voltage source is used, the solenoid can be operated at a higher voltage than that given in the rating, in order to obtain the required power.

These solenoids are subject to overheating during long intervals and a maximum operating time (switch on time + switch off time) of 5 min are observed.

Calculation see pages 20-21.

In order to calculate the power required in your case, the coil current has to be measured. The exact determination of the duty cycle is made in our development laboratories. We would therefore ask you to supply us with the value for coil current.

On request we can supply our rotary solenoids with 2 RS bearings. Please note that in this case, the initial torque M_S will be about 10 % smaller than stated in the data sheets (depending on the size of the solenoid). Solenoids in DS 9420 version with a rotary angle of 95 degrees should not be supplied with 2 RS bearings.

Note: Order code please refer to page 147.

¹⁾ DS 9420 types contain an adjustable return spring

Nennspannung	V DC	24					205					V DC	Voltage rating
ED* LK	%	100	44	21	13	5	100	35	22	13	5	%	ED* LK
Nennstrom	mA	420	875	1.740	2.760	6.490	45	127	195	322	840	mA	Current rating
Nennwiderstand	Ω	57,4	27,4	13,8	8,7	3,7	4.546	1.613	1.050	636	244	Ω	Nominal resistance
D 52, 25°	MA Ncm	6,8	11,4	16,0	18,5	23,5	5,8	11,5	14,5	17,5	23,0	Ncm MA	D 52, 25°
	ME Ncm	11,5	15,3	19,0	21,3	26,0	10,5	15,4	17,5	21,0	25,0	Ncm ME	
D 53, 35°	MA Ncm	5,2	9,4	13,5	16,0	22,0	4,4	9,5	12,2	15,2	21,0	Ncm MA	D 53, 35°
	ME Ncm	10,2	13,5	16,0	17,5	20,0	9,4	13,6	15,2	17,0	19,5	Ncm ME	
D 54, 45°	MA Ncm	3,6	6,8	11,0	13,8	18,8	3,1	6,9	9,6	12,5	18,0	Ncm MA	D 54, 45°
	ME Ncm	9,3	12,5	14,5	16,0	18,0	8,6	12,5	14,0	15,5	17,7	Ncm ME	
D 56, 65°	MA Ncm	2,2	4,4	8,1	10,3	15,5	1,9	4,5	6,7	9,8	14,5	Ncm MA	D 56, 65°
	ME Ncm	8,6	11,5	13,5	14,3	15,0	8,1	11,6	12,8	14,0	15,0	Ncm ME	
D 59, 95°	MA Ncm	0,8	2,2	4,1	5,6	9,8	0,6	2,2	3,3	5,1	9,1	Ncm MA	D 59, 95°
	ME Ncm	7,2	8,9	9,8	9,8	9,2	6,6	9,0	9,6	9,8	9,2	Ncm ME	

* LK = Luftkühlung,
bei Kühlfläche ≥ 300 cm² ist die 1,7fache ED
zulässig

MA = Anfangsdrehmoment
ME = Enddrehmoment (5° vor Drehwinkelende)

Anschlussart: - Litze
- Gerätestecker
Gewicht: ca. 380 g
Dyn. Trägheitsmoment
(Drehmasse): ca. 1,8·10⁻⁶ kg m²
Zeitkonstante: ca. 8–25 ms

Alle Magnete mit MA > 2,5 Ncm sind
mit Rückholfeder MRA ca. 2 Ncm
lieferbar.

Alle Magnete mit MA ≤ 2,5 Ncm sind
mit einer weich eingestellten Rückhol-
feder nach DS9420 mit MRA ca.
0,65 Ncm lieferbar.

Die Betriebsspannung von 205 V DC
ergibt sich nach der Gleichrichtung von
230 V AC mittels Brückengleichrichter.

* By using a cooling surface ≥ 300 cm², the
permissible duty cycle can be extended up to
1.7x normal rating

MA = Initial torque
ME = End torque (5° before end of rotary angle)

Coil terminals: - Flying leads
- Plug
Weight: appr. 380 g
Dyn. moment of
inertia (rotational
mass): appr. 1.8·10⁻⁶ kg m²
Time constant: appr. 8–25 ms

All solenoids with MA > 2.5 Ncm are
available with return spring, with a rating
of MRA approx. 2 Ncm.

All solenoids with MA ≤ 2.5 Ncm are
available with a soft adjustable return
spring according to DS9420, with a
rating of MRA approx. 0.65 Ncm.

The operational voltage of 205 V DC
results from rectifying 230 V AC with a
bridge rectifier.

