

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Date of issue: 3/18/2015 Revision date: 6/27/2016 Version: 2.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : P38-R
Product group : Bodyfiller

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public

Industrial/Professional use spec : Intended for general public

Function or use category : Fillers

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

U-POL LIMITED

Denington Road, Wellingborough

NN8 2QH - UK

T +44 (0) 1933 230310 - F +44 (0) 1933 425797 technical.department@u-pol.com - www.u-pol.com

1.4. Emergency telephone number

Emergency number : +44 (0) 870 8200418

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin corrosion/irritation, Category 2 H315
Serious eye damage/eye irritation, Category 2 H319
Reproductive toxicity, Category 2 H361
Specific target organ toxicity — Repeated exposure, Category 1 H372

Full text of hazard classes and H-statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)





GHS07

GHS08

Signal word (CLP) : Danger Hazardous ingredients : styrene

Hazard statements (CLP) : H315 - Causes skin irritation

H319 - Causes serious eye irritation

H361 - Suspected of damaging the unborn child

H372 - Causes damage to organs (hearing organs) through prolonged or repeated exposure

(Inhalation)

Precautionary statements (CLP) : P102 - Keep out of reach of children

P261 - Avoid breathing fume, vapours

P263 - Avoid contact during pregnancy/while nursing P264 - Wash hands thoroughly after handling

P280 - Wear eye protection, protective clothing, protective gloves

P302+P352 - IF ON SKIN: Wash with plenty of water

7/7/2016 EN (English) SDS Ref.: P38-R 1/7

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

P305 - IF IN EYES: Wash with plenty of water and if necessary take medical advice

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

3.2. Mixture

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
styrene	(CAS No) 100-42-5 (EC no) 202-851-5 (REACH-no) 01-2119457861-32	5 - 23	Flam. Liq. 3, H226 Acute Tox. 4 (Inhalation:dust,mist), H332 Skin Irrit. 2, H315 Eye Irrit. 2, H319 Repr. 2, H361d STOT RE 1, H372

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : Never give anything by mouth to an unconscious person. IF exposed or concerned: Get

medical advice/attention.

First-aid measures after inhalation : Assure fresh air breathing. Allow the victim to rest.

First-aid measures after skin contact : Wash with plenty of soap and water. Wash contaminated clothing before reuse. If skin irritation

occurs: Get medical advice/attention. Get medical advice/attention.

First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to

do. Continue rinsing. If eye irritation persists: Get medical advice/attention. Get medical

advice/attention.

First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries : Suspected of damaging fertility or the unborn child. Causes damage to organs through

prolonged or repeated exposure.

Symptoms/injuries after skin contact : Causes skin irritation.

Symptoms/injuries after eye contact : Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.

Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any

chemical fire. Prevent fire fighting water from entering the environment.

Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Remove ignition sources.

6.1.1. For non-emergency personnel

Protective equipment : Safety glasses. Protective clothing. Gloves.

Emergency procedures : Evacuate unnecessary personnel.

7/7/2016 EN (English) SDS Ref.: P38-R 2/7

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.

Emergency procedures : Ventilate area

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

For containment : Contain leaking substance. Collect spillage.

Methods for cleaning up : On land, sweep or shovel into suitable containers. Minimize generation of dust. Store away

from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection. For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or

smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. Obtain special instructions before use. Do not handle until all safety precautions

have been read and understood. Do not breathe dust, fume.

: Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Ignition sources,

Heat sources. Keep container closed when not in use.

Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight.

Storage temperature : < 25 °C

Special rules on packaging : Keep only in original container.

7.3. Specific end use(s)

Hygiene measures

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

styrene (100-42-5)		
United Kingdom	Local name	Styrene
United Kingdom	WEL TWA (mg/m³)	430 mg/m³
United Kingdom	WEL TWA (ppm)	100 ppm
United Kingdom	WEL STEL (mg/m³)	1080 mg/m³
United Kingdom	WEL STEL (ppm)	250 ppm

8.2. Exposure controls

Personal protective equipment : Avoid all unnecessary exposure.

Materials for protective clothing:

Impermeable clothing

Hand protection:

Wear protective gloves

Eye protection:

Chemical goggles or safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection: Wear appropriate mask

Other information : Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Solid

7/7/2016 EN (English) SDS Ref.: P38-R 3/7

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Appearance : Paste.
Colour : Light grey.
Odour : aromatic.

Odour threshold : No data available pH : No data available Relative evaporation rate (butylacetate=1) : No data available Melting point : No data available Freezing point : No data available Boiling point : No data available : No data available

Flash point : 32 °C

Auto-ignition temperature : No data available
Decomposition temperature : No data available
Flammability (solid, gas) : Non flammable
Vapour pressure : No data available
Relative vapour density at 20 °C : No data available
Relative density : No data available
Density : 1.13 - 1.17

Solubility : insoluble in water, soluble in most organic solvents.

Log Pow : No data available
Viscosity, kinematic : No data available
Viscosity, dynamic : No data available
Explosive properties : No data available
Oxidising properties : No data available
Explosive limits : No data available

9.2. Other information

VOC content : 236 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

Skin corrosion/irritation : Causes skin irritation.
Serious eye damage/irritation : Causes serious eye irritation.

Respiratory or skin sensitisation : Not classified

Additional information : Based on available data, the classification criteria are not met

Germ cell mutagenicity : Not classified

Based on available data, the classification criteria are not met

Carcinogenicity : Not classified

Additional information : Based on available data, the classification criteria are not met

Reproductive toxicity : Suspected of damaging the unborn child.

Specific target organ toxicity (single exposure) : Not classified

7/7/2016 EN (English) SDS Ref.: P38-R 4/7

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Additional information : Based on available data, the classification criteria are not met

Specific target organ toxicity (repeated

exposure)

: Causes damage to organs (hearing organs) through prolonged or repeated exposure

(Inhalation).

Aspiration hazard : Not classified

Additional information : Based on available data, the classification criteria are not met

Potential adverse human health effects and

symptoms

: Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

No additional information available

12.2. Persistence and degradability

_		

Persistence and degradability Not established.

12.3. Bioaccumulative potential

P	3	8-	·R
---	---	----	----

Bioaccumulative potential Not established.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.

Waste disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of

contents/container to Remove waste in accordance with local and/or national regulations.

Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

UN-No. (ADR) : Not applicable
UN-No. (IMDG) : Not applicable
UN-No. (IATA) : Not applicable
UN-No. (ADN) : Not applicable
UN-No. (RID) : Not applicable

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable
Proper Shipping Name (IMDG) : Not applicable
Proper Shipping Name (IATA) : Not applicable
Proper Shipping Name (ADN) : Not applicable
Proper Shipping Name (RID) : Not applicable

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : Not applicable

IMDG

Transport hazard class(es) (IMDG) : Not applicable

IATA

Transport hazard class(es) (IATA) : Not applicable

7/7/2016 EN (English) SDS Ref.: P38-R 5/7

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ADN

Transport hazard class(es) (ADN) : Not applicable

RID

Transport hazard class(es) (RID) : Not applicable

14.4. Packing group

Packing group (ADR) : Not applicable
Packing group (IMDG) : Not applicable
Packing group (IATA) : Not applicable
Packing group (ADN) : Not applicable
Packing group (RID) : Not applicable

14.5. Environmental hazards

Dangerous for the environment : No Marine pollutant : No

Other information : No supplementary information available

14.6. Special precautions for user

- Overland transport

No data available

- Transport by sea

No data available

- Air transport

No data available

- Inland waterway transport

No data available

- Rail transport

No data available

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

VOC content : 236 g/l

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE

COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending

Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:

Acute Tox. 4 (Inhalation:dust,mist) Acute toxicity (inhalation:dust,mist) Category 4

7/7/2016 EN (English) SDS Ref.: P38-R 6/7

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Eye Irrit. 2	Serious eye damage/eye irritation, Category 2			
Flam. Liq. 3	Flammable liqu	Flammable liquids, Category 3		
Repr. 2	Reproductive to	Reproductive toxicity, Category 2		
Repr. 2	Reproductive to	oxicity, Category 2		
Skin Irrit. 2	Skin corrosion/	Skin corrosion/irritation, Category 2		
STOT RE 1	Specific target	Specific target organ toxicity — Repeated exposure, Category 1		
H226	Flammable liqu	Flammable liquid and vapour		
H315	Causes skin irr	Causes skin irritation		
H319	Causes serious	Causes serious eye irritation		
H332	Harmful if inha	Harmful if inhaled		
H361	Suspected of c	Suspected of damaging fertility or the unborn child		
H361d	Suspected of c	Suspected of damaging the unborn child		
H372	Causes damag	Causes damage to organs through prolonged or repeated exposure		
Skin Irrit. 2	H315	Calculation method		
Eye Irrit. 2	H319	Calculation method		
Repr. 2	H361	Calculation method		
STOT RE 1	H372	Calculation method		

UPOL SDS EU (no product code)

The information contained within this Safety Data Sheet (SDS) is believed to be correct as of the date issued however it is subject to change from time to time. It does not purport to be all inclusive or exhaustive and shall only be used as a guide. U-POL makes no warranties, expressed or implied, including but not limited to, any implied warranty of fitness for a given purpose or usage. It is the Buyers responsibility to ensure the suitability of the products for their own use and to check the information is up to date. U-POL cannot be held responsible for the suitability of use for any of its products, considering the wide range of factors such as application, substrates and handling methods. Since these conditions of use are outside of our control, the company shall not be held liable for any damage resulting from handling or from contact with the product detailed. Moreover, addition of reducers, hardeners or other additives over and above U-POL's recommendations for use, may substantially alter the composition and hazards of the product. U-POL data sheets are available via the U-POL website at WWW.U-POL.COM.

7/7/2016 EN (English) SDS Ref.: P38-R 7/7