



SITOR FUSE-LINK FOR SEMICONDUCTOR
PROTECTION 100A AR 1000V SIZE 3 KNIFE
CONTACT FOR BOLTED CONNECTION 130MM

Figure similar

Model		
product brand name		SENTRON
Design of an identification indicator		front indicator
Design of the fuse link		SITOR, LV HRC design
General technical data		
Size of fuse system / acc. to DIN EN 60269-1		NH3
Operating class of the fuse link		aR
circuit-breaker / Design		3NE
Switching capacity		
Switching capacity current		
• acc. to IEC 60947-2 / Rated value	kA	100
Dissipation		
Active power loss		
• for rated value of the current / with AC / in hot operating state / per pole	W	25
Electricity		
rated current I _n / IEC, DIN/VDE / at 40 Cel	A	100
Current / with AC / Rated value	A	100
Mechanical Design		
mounting position		Any, preferably vertical
Environmental conditions		
Ambient temperature		
• minimum	°C	-20

• maximum

°C 50

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NE34210C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NE34210C/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE34210C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015