

NEOZED-FUSE LINK 400V GL/GG,GR.D02, 32A,
COLLAPSIBLE BOX



Figure similar

Model		
product brand name		SENTRON
Product variations		Pack of 10
Design of the fuse link		NEOZED fuse links
General technical data		
Size of fuse system / acc. to DIN EN 60269-1		D02
Operating class of the fuse link		gG
circuit-breaker / Design		5SE2
Protection class		
Protection class IP		IP20, with connected conductors
Switching capacity		
Switching capacity current / acc. to IEC 60947-2 / Rated value	kA	50
Dissipation		
Active power loss • for rated value of the current / with AC / in hot operating state / per pole	W	1.7
Electricity		
rated current I _n / IEC, DIN/VDE / at 40 Cel	A	30.4
Current / with AC / Rated value	A	32
Mechanical Design		
mounting position		Any, preferably vertical
Environmental conditions		

Ambient temperature

- minimum
- maximum

°C	-5
°C	40

General Product Approval



Test Certificates

[Special Test Certificate](#)

[other](#)

[Type Test Certificates/Test Report](#)

other

[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SE2332>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SE2332/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SE2332

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015