



THIS IS A C.A.D. GENERATED DRAWING  
DO NOT MAKE MANUAL REVISIONS TO MASTER.



\* UNLESS OTHERWISE SPECIFIED TOLERANCES  
ON DECIMAL IS: ANGLE = ± 5°  
0.5-5 = ±0.2  
5-30 = ±0.4  
UNIT: MM 30-120 = ±0.6  
120-315 = ±1.0



BNC MALE  
CENTER CONTACT: BRASS / GOLD PLATE  
BODY: ZINC ALLOY / NICKEL PLATE  
SHELL: ZINC ALLOY / NICKEL PLATE

INNER CONDUCTOR ○ ○ ALLIGATOR CLIP / RED

BRAID ○ ○ ALLIGATOR CLIP / BLACK

FREQUENCY	400 MHz
ATTENUATION	1 dB/M MIN.
CAPACITANCE	101 pF/M
MAX. VOLTAGE	1.5 KV/RMS MIN.

NOTE:  
1. BNC male - punch ø8.3

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN	DATE
JDHNNY	04-24-13
APPROVED	DATE



THIS SERIES FULLY CONFORMS TO THE  
EUROPEAN UNION DIRECTIVES 2002/95/EC  
AND 2002/96/EC FOR ROHS COMPLIANCY.



MH CONNECTORS LTD.

SCALE	SHEET OF	REV:
	1 OF 1	1.0
DRAWING No		
GEX373-1M		