

2:1 Heat Shrink Tubing Kit Green/Yellow

pro-POWER

RoHS
Compliant



Features

- Halogen Free
- Operating temperature -55°C to +125°C
- Minimum shrink temperature 70°C
- Full recovery temperature: 125°C
- Shrink Ratio 2:1
- Colour: Green/Yellow

Applications

Dual-colour green and yellow striped polyolefin tubing primarily used to identify “ground” wires. It is flexible and flame-retardant with permanent colour properties, making it easy to install and identify. Used for light-duty harnessing and ground wire identification.

Kit Contains

- 2:1 normal wall, 3.2mm (50mm × 75pcs)
- 2:1 normal wall, 4.8mm (50mm × 30pcs)
- 2:1 normal wall, 9.5mm (50mm × 50pcs)
- 2:1 normal wall, 12.7mm (70mm × 25pcs)

Technical Data

Property	Test Method	Typical Data
Tensile Strength	ASTM D2671	≥10.4 Mpa
Ultimate Elongation	ASTM D2671	≥200%
Longitudinal Shrinkage	UL 224	±8%
Heat Aging Tensile Strength Ultimate Elongation	158°C, 168hrs	≥7.3 Mpa ≥100%
Heat shock	250°C, 4hrs	No cracking, No dripping
Cold Bend	-30°C, 1hrs	No cracking
Flammability	UL224 VW-1	Pass
Dielectric Strength (kv/mm)	GB/T1408	15 (min.)
Volume Resistivity (ohm-cm)	GB/T1410	1x10 ¹⁴ (min.)
Copper Stability	UL224	No corrosion
Copper Corrosion	UL224	No Corrosion

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

pro-POWER

2:1 Heat Shrink Tubing Kit

Green/Yellow



Product Dimensions

Size		As supplied	After Recovery	
Inch	mm	Internal diameter Min.(mm)	Internal diameter Max.(mm)	Wall thickness(mm)
1/8	3.2	3.5 ±0.4	1.5	0.38 ±0.1
3/16	4.8	5 ±0.4	2.3	0.45 ±0.1
3/8	9.5	9.5 ±0.5	4.5	0.55 ±0.1
1/2	12.7	12.5 ±0.5	6	0.6 ±0.1

Part Number Table

Description	Part Number
Heat Shrink Tubing Kit, Polyolefin, 2:1, Normal Wall, Green/Yellow, 180 Pcs	HSKIT2:1G/Y

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

