
S2FP103

Part Number



- Locking force of 1150 N
- Performance Level: Cat. 4 PL e
- Power to unlock principle

The electromechanical safety switch with lock function is distinguished by a high locking force of 1150 N. As a result, only one safety switch with lock function is required in order to fulfill a safety level of category 4 PL e (EN ISO 13849-1). The safety level, as well as reaction time and risk time, remain unchanged when connected in series. Extensive diagnosis functions enhance system availability and simplify installation and maintenance. The unique star handle operating concept is especially well-suited for rotary and sliding doors. Thanks to RFID encoding and an actuator with teach-in function, the safety switch with lock function demonstrates high levels of protection against manipulation.



Technical Data


Electrical Data			
Sensor Type	Locking unit		
Supply Voltage	20,426,4 V DC		
Response Time	≤ 100 ms		
Risk time	≤ 200 ms		
Temperature Range	060 °C		
Storage temperature	-1090 °C		
Safety Output	OSSD		
No. Safety Outputs (OSSDs)	2		
PNP Safety Output/Switching Current	250 mA		
Number of Signal Outputs	1		
PNP signal output switching current	50 mA		
Short Circuit Protection	yes		
Protection Class	III		
Mechanical Data			
Housing Material	Plastic		
Degree of Protection	IP66/IP67/IP69		
Connection	M12 × 1; 8-pin		
Latching Force, typical	25 / 50 N		
Safety-relevant Data			
Operating principle	RFID		
Coding	Individual, teachable		
Performance Level (EN ISO 13849-1)	Cat. 4 PL e		
PFHD	5,20 × E-10 1/h		
Safety Integrity Level (EN 61508)	SIL3		
Safety Integrity Level (EN 62061)	SILCL3		
PDDB (EN 60947-5-3)	yes		
Locking Device	Power to unlock principle		
Locking Force F (Zh)	1150 N		
Function			
Series Connection	yes		
Actuator monitored	yes		
Mechanical Detent Mechanism	yes		
Detent Mechanism	yes		
Auxiliary release	yes		
Applicable actuator	S2FP200		
Connection Diagram No.	P03		
Suitable Connection Equipment No.	89		
Suitable Mounting Technology No.	850		


Complementary Products

Safety Relay SR4B3B01S, SR4D3B01S

Software







_egen	nd		PT	Platinum measuring resistor		Encoder A/Ā (TTL)	
+	Supply Voltage +		nc	not connected	ENBRS422	Encoder B/B (TTL)	
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A	
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENB	Encoder B	
Α		IO)	W	Trigger Input	Amin	Digital output MIN	
Ā		IC)	W -	Ground for the Trigger Input	Амах	Digital output MAX	
٧		IO)	0	Analog Output	Аок	Digital output OK	
V		IC)	0-	Ground for the Analog Output	SY In	Synchronization In	
E	Input (analog or digital)		BZ	Block Discharge	SY OUT	Synchronization OUT	
Т	Teach Input		Awv	Valve Output	OLT	Brightness output	
Z	Time Delay (activation)		а	Valve Control Output +	М	Maintenance	
S	Shielding		b	Valve Control Output 0 V	rsv	reserved	
RxD	Interface Receive Path		SY	Synchronization	Wire Co	olors according to IEC 60757	
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black	
RDY	Ready		E+	Receiver-Line	BN	Brown	
GND	Ground		S+	Emitter-Line	RD	Red	
CL	Clock		÷	Grounding	OG	Orange	
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow	
0	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green	
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue	
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet	
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey	
Signal	Signal Output		Mag	Magnet activation	WH	White	
BI_D+/-	Ethernet Gigabit bidirect. data lir	ne (A-D)	RES	Input confirmation	PK	Pink	
	Encoder 0-pulse 0-0 (TTL)		EDM	Contactor Monitoring	GNYE	Green/Yellow	











