



Material Specification

Turcon[®] T24

Material

A high grade composition of virgin PTFE compounded with carbon.

Colour

Black.

The colour of the material may have variations in shading.

Property	Test Conditions	Standard	Unit	Value
Specific Gravity	23°C	ASTM D 792	g/cm ³	2.13 max. 2.09 min.
Tensile Stress @ Break	23°C	ASTM D 4894	MPa	22 min.
Tensile Elongation @ Break	23°C	ASTM D 4894	%	225 min.
Ball Indentation Hardness	23°C	ISO 2039-1	MPa	28 min.

Reg. No. 0404/T24

- ® Registered Trademark of Trelleborg Shamban DK (Trelleborg Sealing Solutions Denmark A/S).
- ® The turquoise colour is a Registered Trademark for products of B+S.
- © Copyright 2004 - Trelleborg Shamban DK.

This is an uncontrolled copy of the Trelleborg Shamban DK Material Specifications.

Trelleborg Shamban DK assumes no responsibility for performance, expressed or implied, and warranty is limited to replacement of product for defects in material and workmanship.

Based upon our ongoing seals and materials development programme, Trelleborg Shamban DK reserve the right to change properties contained within this Material Specification, in the light of experience, without further notice.