

## Part Number: 7958A



DataTuff® Cat 5e, (4 pr) 24 AWG Solid BC, PO/PVC, Foil Shld, EtherNet/IP, CMR, 600 V AWM, MSHA

### Product Description

Four Cat 5e 24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, overall Beldfoil® shield (100% coverage), industrial grade oil- and UV-resistant PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, 200MHz Category 5e, Industrial Ethernet, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, CMX - Outdoor, RJ-45 Compatible*
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Total Number of Conductors:	8
-----------------------------	---

##### Insulation

Material	Nominal Wall Thickness
PO - Polyolefin	0.01 in

##### Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

##### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

##### Outer Jacket Material

Material	Nominal Diameter	Ripcord
Industrial Grade PVC - Polyvinyl Chloride	0.265 in	No

#### Electrical Characteristics

##### Capacitance

Max. Capacitance Unbalance	Nom.Mutual Capacitance
150 pF/ft	15 pF/ft

Shielding:	Beldfoil® Shield
------------	------------------

#### Construction and Dimensions

Total Number of Pairs:	4
------------------------	---

## Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
9.38 Ohm/1000ft	3 %

## Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
538 ns/100m	45 ns/100m	70 %

## High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	65.3 dB	62.3 dB	63 dB	60 dB	63.8 dB	60.8 dB	20 dB	20 dB	100 ± 15 Ohm	
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	51 dB	49 dB	51.7 dB	48.7 dB	23.6 dB	23.6 dB	100 ± 15 Ohm	
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46 dB	43 dB	45.7 dB	42.7 dB	25.4 dB	25.4 dB	100 ± 15 Ohm	
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43 dB	41 dB	43.8 dB	40.8 dB	26 dB	26 dB	100 ± 15 Ohm	
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	39 dB	36 dB	39.7 dB	36.7 dB	26 dB	26 dB	100 ± 15 Ohm	
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.7 dB	34.7 dB	26 dB	26 dB	100 ± 15 Ohm	
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	25.5 dB	25.5 dB	100 ± 15 Ohm	
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31 dB	28 dB	33.9 dB	30.9 dB	25 dB	25 dB	100 ± 15 Ohm	
62.5 MHz	17 dB/100m	38.4 dB	35.4 dB	22 dB	19 dB	27.8 dB	24.8 dB	23.5 dB	23.5 dB	100 ± 15 Ohm	
100 MHz	22 dB/100m	35.3 dB	32.3 dB	14 dB	11 dB	23.8 dB	20.8 dB	22.5 dB	22.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
200 MHz	32.4 dB/100m		27.8 dB		1 dB		14.7 dB			100 ± 25 Ohm	
1 MHz											
4 MHz											
8 MHz											
10 MHz											
16 MHz											
20 MHz											
25 MHz											
31.25 MHz											
62.5 MHz											
100 MHz											
200 MHz											

## Voltage

UL Description	UL Voltage Rating
	300V RMS
Appliance Wiring Material	600 V RMS

## Applicable Standards & Environmental Programs

CEC/C(UL) Specification:	CMR
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CPR Euroclass:	Eca
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e, UL verified to Category 5e, Ethernet/IP™ Compliant
Patent:	<a href="http://www.belden.com/p">http://www.belden.com/p</a>

## Standards

ISO/IEC Compliance:	ISO/IEC 11801 ed 2.1 (2008) Class D
ANSI/TIA Category:	Category 5e
NEC/(UL) Specification:	CMR, CMX-OUTDOOR, UL 444

UL AWM Style:	UL Style 21047
---------------	----------------

## Flame Test

CSA Flammability:	FT4
UL Flammability:	UL1666 Riser

## Safety

UL Voltage Rating:	300 V RMS
--------------------	-----------

## Suitability

Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

## Mechanical Characteristics

Storage Temp Range:	-40°C To +75°C
Installation Temp Range:	-25°C To +75°C
Operating Temp Range:	-40°C To +75°C
Bulk Cable Weight:	32(lbs/1000ft)
Max Recommended Pulling Tension:	35(lbs)
Min Bend Radius/Minor Axis:	0.5(in)

## Temperature Range

UL Temp Rating:	60°C
-----------------	------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## History

### Variants

Item #	Color
7958A 0101000	BLACK
7958A 0102000	BLACK
7958A 0061000	BLUE
7958A 0061000	BLUE
7958A 0081000	GRAY
7958A 0021000	RED
7958A 1NH1000	TEAL

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.