



Fatigue Fighter II®

The ultimate in durable anti-fatigue mats

- Dual fused layer construction for superior comfort and durability.
- Tough PVC foam textured top surface for excellent resilience against wear and tear.
- Low density under layer provides extremely effective underfoot cushioning.
- Exceptional fatigue-relief properties – a real investment for the workplace.
- Ideal for demanding locations, especially where regular turning is involved.
- Tapered edges to reduce trip hazards.
- Range of colours available.

Product height: 12.5mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.6 x 0.9	3	17.5 x 17.5 x 75	Boxed	1	20	Black	FF010001
0.6 x 18.3	45	54 x 54 x 100	Boxed	1	4	Black	FF010005
0.6 x per linear metre	3	3 x 3 x 60	Roll	1	N/A	Black	FF010005C
0.9 x 1.5	6	20.5 x 22 x 100	Boxed	1	30	Black	FF010002
0.9 x 3.65	14	24 x 24 x 92	Boxed	1	16	Black	FF010004
0.9 x 18.3	72	54 x 54 x 100	Boxed	1	4	Black	FF010003
0.9 x per linear metre	4	4 x 4 x 90	Roll	1	N/A	Black	FF010003C
1.2 x 18.3	90	60 x 60 x 130	Boxed	1	4	Black	FF010006
1.2 x per linear metre	5	5 x 5 x 120	Roll	1	N/A	Black	FF010006C
0.9 x 18.3	72	54 x 54 x 100	Boxed	1	4	Blue	FF020003
						Green	FF040003
0.9 x per linear metre	4	4 x 4 x 90	Roll	1	N/A	Blue	FF020003C
						Green	FF040003C

Material:	Virgin Closed Cell PVC (Foam)
Surface Finish:	Pebble wear resistant top surface
Product Height:	12.5mm nominal
Operating Temperature:	0° to 60° C
Resistance to Chemicals:	PVC is resistant to many different chemicals, alkalis and general industrial chemicals. Resist alcohol's, aliphatic hydrocarbons, oils, weak acids, strong mineral acids and alkalis. Resists oil and grease if properly cleaned. Does not resist organic solvents, ketones, esters and aromatic hydrocarbons. Please contact the sales office for more specific details.
Environmental Resistance:	Suitable for dry indoor environments.
UV Resistance:	N/A
Typical Applications:	Production lines, assembly areas, packing stations, workbenches and retail cashier stations.
Installation Method:	Loose lay.
Cleaning Method:	Brush/mop the top surface.

Continued on next page

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

+44 (0)116 240 1088
sales@cobaeeurope.com
www.cobaeeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

+49 (2161) 2945-0
verkauf@cobaeeurope.de
www.cobaeeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamence 11
SK-013 06

+421 41 507 11 12
sales@cobaeeurope.sk
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.

Product Performance:	Fatigue: ●●●●● Slip Resistance: ●● Wear: ●●●● Low ‡ High ● → ●●●●●
Flame Retardancy:	Conforms to BS EN 13501-1:2002 Class Efl
Country of Origin:	USA
Guarantee:	3 year guarantee when used in a dry environment

End of document

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

☎ +44 (0)116 240 1088
✉ sales@cobaeeurope.com
🌐 www.cobaeeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

☎ +49 (2161) 2945-0
✉ verkauf@cobaeeurope.de
🌐 www.cobaeeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamenec 11
SK-013 06

☎ +421 41 507 11 12
✉ sales@cobaeeurope.sk
🌐 www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.