

Cemented carbide T-groove cutter

ORION[®]

Application:

For making T-slots conforming to DIN 650

Execution:

- Straight shank according to DIN 1835 A
- Stable cemented carbide cutters
- Cross-toothing
- Corners 0.3 mm x 45°, chamfered
- In accordance with DIN 650



Art. no.	16525 080
Brand	ORION
Manufacturer Part Number	16525080
Cutting material	Carbide
Surface	Uncoated
Type	N
Number of cutting edges	6 PCS
Tool holding device	HA parallel shank
Cutting edge diameter	16 mm
Width of cutting edge	8 mm
Suitable for T-groove	8 mm
Length	63 mm
Neck diameter	7 mm
Shank diameter	10 mm
fz steel 1000	0.03 mm
Gross Weight	0.041 kg
Product Group	165

EAN

4039247104062