

Machine lamp LED pro ML 1210 B

Voltage 230 V, 50 Hz, suppressed, for workstations and machines



Execution:

- Model ML 1210 B with LED module 10.5 W behind frosted glass cover
- Beam angle 150°, light colour 6500 K, luminous flux 1170 lumens, 400 lux (1 m)
- With 3 m connection cable, flexible hose length 500 mm
- Energy efficiency class F
- Made in Germany, TÜV GS tested, protection class II

Delivery:

Incl. adhesive magnet and table clamp

Art. no.	56870 210
Brand	HEDI
Manufacturer Part Number	ML1210B
Power rating	10.5 W
Arm length	500 mm
Luminous flux	1170 lm
IP protection class	IP 64
Gross Weight	2.272 kg
Product Group	7AG



EAN

4003644001590