

**Bolt-type screw terminals  
WF 12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Klippon® Connect with stud Technology**

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

**General ordering data**

Type	WF 12
Order No.	<a href="#">1780880000</a>
Version	Bolt-type screw terminals, Feed-through terminal, Rated cross-section: 120 mm <sup>2</sup> , Threaded stud connection
GTIN (EAN)	4032248219360
Qty.	20 pc(s).

Creation date 11 March 2020 11:28:25 CET

Catalogue status 06.03.2020 / We reserve the right to make technical changes.

**Bolt-type screw terminals  
WF 12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	33.8 mm	Width (inches)	1.331 inch
Height	67 mm	Height (inches)	2.638 inch
Depth	70.5 mm	Depth (inches)	2.776 inch
Net weight	102.6 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

**Material data**

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

**System specifications**

Version	Single-stud terminals	End cover plate required	No
Number of levels	1	Number of clamping points per level	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35		

**Additional technical data**

Explosion-tested version	No	Number of similar terminals	1
Open sides	Open	Type of mounting	Snap-on

**CSA rating data**

Certificate No. (CSA)	200039-1244019	Current size C (CSA)	320 A
Voltage size C (CSA)	1000 V	Wire cross section max. (CSA)	250 kcmil
Wire cross section min. (CSA)	10 AWG		

**Conductors for clamping (rated connection)**

2 x cable lugs DIN 46 234	6 to 120 mm <sup>2</sup>	2 x cable lugs DIN 46 235	10...95 mm <sup>2</sup>
Cable lug to DIN 46234	6...120 mm <sup>2</sup>	Cable lug to DIN 46235	10...95 mm <sup>2</sup>
Clamping range, max.	120 mm <sup>2</sup>	Clamping range, min.	6 mm <sup>2</sup>
Number of connections	1	Stud size for spade connection	M 12
Tightening torque, max.	31 Nm	Tightening torque, min.	14 Nm
Type of connection	Threaded stud connection		

**Rating data**

Rated cross-section	120 mm <sup>2</sup>	Rated voltage	1,000 V
Voltage with epoxy resin partition plate	2,300 V	Rated current	269 A
Current at maximum wires	269 A	Volume resistance according to IEC 60947-7-x	0.12 mΩ
Power loss in accordance with IEC 60947-7-x	8.61 W	Rated impulse withstand voltage	8 kV
Impulse voltage with epoxy resin partition plate	12 kV	Pollution severity	3

Creation date 11 March 2020 11:28:25 CET

**Bolt-type screw terminals  
WF 12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Stud connection**

2 x cable lugs DIN 46 234	6 to 120 mm <sup>2</sup>	2 x cable lugs DIN 46 235	10...95 mm <sup>2</sup>
Cable lug to DIN 46234	6...120 mm <sup>2</sup>	Cable lug to DIN 46235	10...95 mm <sup>2</sup>
Impulse voltage with epoxy resin partition plate	12 kV	Stud size for spade connection	M 12
Tightening torque, max.	31 Nm	Tightening torque, min.	14 Nm
Voltage with epoxy resin partition plate	2,300 V		

**UL rating data**

Certificate No. (UR)	E60693	Conductor size Factory wiring max. (UR)	250 kcmil
Conductor size Factory wiring min. (UR)	10 AWG	Conductor size Field wiring max. (UR)	250 kcmil
Conductor size Field wiring min. (UR)	10 AWG	Current size C (UR)	255 A
Voltage size C (UR)	1000 V		

**Classifications**

ETIM 6.0	EC000897	ETIM 7.0	EC000897
eClass 9.0	27-14-11-20	eClass 9.1	27-14-11-20
eClass 10.0	27-14-11-20	UNSPSC	30-21-18-01

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">CB Test Certificate</a> <a href="#">CB Certificate</a> <a href="#">DE_PT1004_20160418_842_ISSUE01.pdf</a>
Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>

**Safety note**

 Safety notice [Safety Information](#)

**Data sheet**

**Bolt-type screw terminals  
WF 12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

