




TERMINAL MODULE FOR ET 200S RS FOR REVERSING STARTER, WITHOUT FEEDER CONNECTION

Figure similar

General technical data:		
Product designation		Terminal module
Product type designation		TM-RS90-S31
Design of the product		for RS1-x, with energy bus bushing
Mounting height	mm	264
Installation width	mm	90
Installation depth	mm	100
Protection class IP		IP20
Insulation voltage Rated value	V	690
Operating voltage		
• with AC Rated value	V	500
Surge voltage resistance Rated value	V	6 000
Operating current Rated value	A	40
Operating frequency		
• 1 Rated value	Hz	50
• 2 Rated value	Hz	60
Type of connectable conductor cross-section		
• solid		1x 10 mm ² , 2x (1 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²)
• finely stranded with core end processing		2x (1 ... 2.5 mm ²), 2x (2.5 ... 6 mm ²), acc. to IEC 60947
• for AWG conductors		
— solid		2x (14 ... 10)
— stranded		2x (14 ... 10)
Installation/ mounting/ dimensions:		
Size of the screwdriver tip		Standard screwdriver Size 2

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)<http://www.siemens.com/industrial-controls/catalogs>**Industry Mall (Online ordering system)**<http://www.siemens.com/industrymall>**Cax online generator**<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK19030AC10>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<http://support.automation.siemens.com/WW/view/en/3RK19030AC10/all>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK19030AC10&lang=en>



last modified:

15.01.2015