



UNDervOLTAGE RELEASE, AC 400V/50HZ, AC 440V/60HZ WITH SPRING-L. CONNECTION, FOR CIRCUIT-BREAKERS 3RV2

General technical data:		
product brand name		SIRIUS
Product designation		undervoltage release
Size of the circuit-breaker		S00, S0, S2
Design of the product		<kein Wert>
Suitability for use		motor circuit breaker
Protection class IP on the front		IP20
Design of short-circuit protection		fuse
Degree of pollution		3
Insulation voltage Rated value	V	690
Insulation voltage with degree of pollution 3 Rated value	V	690
Ambient temperature		
• during storage	°C	-50 ... +80
• during operation	°C	-20 ... +60
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		F
Equipment marking acc. to DIN EN 61346-2		F

Auxiliary circuit:		
Number of NC contacts for auxiliary contacts instantaneous contact		0
Number of NO contacts for auxiliary contacts instantaneous contact		0
Number of NO contacts for auxiliary contacts leading contact		0

Number of CO contacts of the auxiliary contacts instantaneous contact		0
---	--	---

#### Control circuit/ Control:

<b>Type of voltage of the control supply voltage</b>		AC
<b>Control supply voltage frequency</b>		
<ul style="list-style-type: none"> <li>• 1 <ul style="list-style-type: none"> <li>— Rated value</li> <li>— Initial rated value</li> <li>— Final rated value</li> </ul> </li> <li>• 2 Rated value</li> </ul>	<ul style="list-style-type: none"> <li>Hz</li> <li>Hz</li> </ul>	<ul style="list-style-type: none"> <li>&lt;kein Wert&gt;</li> <li>50</li> <li>60</li> <li>&lt;kein Wert&gt;</li> </ul>
<b>Control supply voltage</b>		
<ul style="list-style-type: none"> <li>• 1 <ul style="list-style-type: none"> <li>— for DC <ul style="list-style-type: none"> <li>— Rated value</li> <li>— Initial rated value</li> <li>— Final rated value</li> </ul> </li> <li>— with AC <ul style="list-style-type: none"> <li>— at 50 Hz Rated value</li> <li>— at 50 Hz Initial rated value</li> <li>— at 50 Hz Final rated value</li> <li>— at 60 Hz Rated value</li> <li>— at 60 Hz Final rated value</li> <li>— at 60 Hz Initial rated value</li> </ul> </li> </ul> </li> <li>• 2 <ul style="list-style-type: none"> <li>— for DC Rated value</li> <li>— with AC <ul style="list-style-type: none"> <li>— at 50 Hz Rated value</li> <li>— at 60 Hz Rated value</li> </ul> </li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>V</li> <li>V</li> </ul>	<ul style="list-style-type: none"> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>400</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>440</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> </ul>

#### Installation/ mounting/ dimensions:

<b>Mounting type</b>		snap-on mounting
<b>Width</b>	mm	18.5
<b>Height</b>	mm	90
<b>Depth</b>	mm	68
<b>Required spacing with side-by-side mounting</b>		
<ul style="list-style-type: none"> <li>• forwards</li> <li>• Backwards</li> <li>• upwards</li> <li>• downwards</li> <li>• at the side</li> </ul>		<ul style="list-style-type: none"> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> <li>&lt;kein Wert&gt;</li> </ul>
<b>Required spacing for grounded parts</b>		
<ul style="list-style-type: none"> <li>• forwards</li> </ul>		<kein Wert>

- Backwards
- upwards
- at the side
- downwards

<kein Wert>  
<kein Wert>  
<kein Wert>  
<kein Wert>

#### Required spacing for live parts





- forwards
- Backwards
- upwards
- downwards
- at the side

<kein Wert>  
<kein Wert>  
<kein Wert>  
<kein Wert>  
<kein Wert>

#### Certificates/ approvals:


##### Certificate of suitability

CE / UL / CSA

General Product Approval	Declaration of Conformity	Test Certificates		Shipping Approval
 CSA	 UL	 EG-Konf.	<a href="#">Type Test Certificates/Test Report</a>	<a href="#">Special Test Certificate</a>  ABS

#### Shipping Approval

 BUREAU VERITAS	 DNV	 GL	 LRS	 PRS	 RINA
---	--	---	--	--	---

Shipping Approval	other		
 RMRS	<a href="#">Environmental Confirmations</a>	 VDE	<a href="#">other</a>

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RV29022AV0>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RV29022AV0/all>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RV29022AV0&lang=en>



last modified:

09.03.2015