

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name: **Kalibrierlösung CLY11-D 12,64 mS**

Synonym: *Calibration standard CLY11-D 12.64 mS*

Article number: 50081905

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Product category *PC21 Laboratory chemicals*

Application of the substance / the mixture *Laboratory chemicals*

### 1.3 Details of the supplier of the safety data sheet

#### Manufacturer/Supplier:

*Endress+Hauser*

*Conducta GmbH+Co. KG*

*Dieselstraße 24*

*D-70839 Gerlingen*

#### Further information obtainable from:

*Phone: +49 (0)7156 209-10117*

*E-Mail: MSDS.PCC@endress.com*

1.4 Emergency telephone number: *Phone: +49(0)6131-19240*

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

**Classification according to Regulation (EC) No 1272/2008**

*The product is not classified, according to the CLP regulation.*

### 2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 *Void*

Hazard pictograms *Void*

Signal word *Void*

Hazard statements *Void*

### 2.3 Other hazards

*The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds or formaldehydes.*

#### Results of PBT and vPvB assessment

**PBT:** *Not applicable.*

**vPvB:** *Not applicable.*

## SECTION 3: Composition/information on ingredients

### 3.2 Mixtures

Description: *aqueous solution*

Dangerous components: *Void*

Additional information: *For the wording of the listed hazard phrases refer to section 16.*

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

General information: *No special measures required.*

After inhalation: *Supply fresh air; consult doctor in case of complaints.*

After skin contact: *Generally the product does not irritate the skin.*

After eye contact: *Rinse opened eye for several minutes under running water.*

After swallowing: *If symptoms persist consult doctor.*

**Trade name: Kalibrierlösung CLY11-D 12,64 mS**

(Contd. of page 1)

**4.2 Most important symptoms and effects, both acute and delayed***No further relevant information available.***4.3 Indication of any immediate medical attention and special treatment needed***No further relevant information available.***SECTION 5: Firefighting measures****5.1 Extinguishing media****Suitable extinguishing agents:***CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.***For safety reasons unsuitable extinguishing agents:** *no further information***5.2 Special hazards arising from the substance or mixture** *No further relevant information available.***5.3 Advice for firefighters** *No further relevant information available.***Protective equipment:** *No special measures required.***SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures** *Wear protective clothing.***6.2 Environmental precautions:** *Dilute with plenty of water.***6.3 Methods and material for containment and cleaning up:***Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).***6.4 Reference to other sections***No dangerous substances are released.**See Section 7 for information on safe handling.**See Section 8 for information on personal protection equipment.**See Section 13 for disposal information.***SECTION 7: Handling and storage****7.1 Precautions for safe handling** *No special measures required.***Information about fire - and explosion protection:** *No special measures required.***7.2 Conditions for safe storage, including any incompatibilities****Storage:****Requirements to be met by storerooms and receptacles:** *No special requirements.***Information about storage in one common storage facility:** *Not required.***Further information about storage conditions:** *None.***Storage class:** 12**7.3 Specific end use(s)** *No further relevant information available.***SECTION 8: Exposure controls/personal protection****8.1 Control parameters****Ingredients with limit values that require monitoring at the workplace:***The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.***Additional information:** *The lists valid during the making were used as basis.***8.2 Exposure controls****Appropriate engineering controls** *No further data; see item 7.***Individual protection measures, such as personal protective equipment****General protective and hygienic measures:***The usual precautionary measures are to be adhered to when handling chemicals.***Respiratory protection:** *Not required.***Hand protection** *No chemical-protective gloves required.*

(Contd. on page 3)

Trade name: Kalibrierlösung CLY11-D 12,64 mS

(Contd. of page 2)

**Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

**Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

**Eye/face protection** Not required.

**Body protection:** Protective work clothing

**SECTION 9: Physical and chemical properties****9.1 Information on basic physical and chemical properties****General Information**

<b>Physical state</b>	Fluid
<b>Colour:</b>	Colourless
<b>Odour:</b>	Odourless
<b>Odour threshold:</b>	Not determined.
<b>Melting point/freezing point:</b>	0 °C
<b>Boiling point or initial boiling point and boiling range</b>	100 °C
<b>Flammability</b>	Not applicable.
<b>Lower and upper explosion limit</b>	
<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.
<b>Flash point:</b>	Not applicable.
<b>Decomposition temperature:</b>	Not determined.
<b>pH at 20 °C</b>	>6
<b>Viscosity:</b>	
<b>Kinematic viscosity</b>	Not determined.
<b>Dynamic:</b>	Not determined.
<b>Solubility</b>	
<b>water:</b>	Fully miscible.
<b>Partition coefficient n-octanol/water (log value)</b>	Not determined.
<b>Vapour pressure at 20 °C:</b>	23 hPa
<b>Density and/or relative density</b>	
<b>Density at 20 °C:</b>	1.009 g/cm <sup>3</sup>
<b>Relative density</b>	Not determined.
<b>Vapour density</b>	Not determined.

**9.2 Other information****Appearance:**

**Form:** Fluid

**Important information on protection of health and environment, and on safety.****Auto-ignition temperature:**

Product is not selfigniting.

**Explosive properties:**

Product does not present an explosion hazard.  
Not determined.

**Solvent content:**

**Water:** >90.0 %

**Solids content:** 0.0 %

**Change in condition**

**Evaporation rate** Not determined.

(Contd. on page 4)

Trade name: Kalibrierlösung CLY11-D 12,64 mS

(Contd. of page 3)

**Information with regard to physical hazard****classes**

Explosives	Void
Flammable gases	Void
Aerosols	Void
Oxidising gases	Void
Gases under pressure	Void
Flammable liquids	Void
Flammable solids	Void
Self-reactive substances and mixtures	Void
Pyrophoric liquids	Void
Pyrophoric solids	Void
Self-heating substances and mixtures	Void
Substances and mixtures, which emit flammable gases in contact with water	Void
Oxidising liquids	Void
Oxidising solids	Void
Organic peroxides	Void
Corrosive to metals	Void
Desensitised explosives	Void

**SECTION 10: Stability and reactivity****10.1 Reactivity** *No further relevant information available.***10.2 Chemical stability****Thermal decomposition / conditions to be avoided:***No decomposition if used according to specifications.***10.3 Possibility of hazardous reactions** *No dangerous reactions known.***10.4 Conditions to avoid** *No further relevant information available.***10.5 Incompatible materials:** *No further relevant information available.***10.6 Hazardous decomposition products:** *No dangerous decomposition products known.***SECTION 11: Toxicological information****11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008****Acute toxicity** *Based on available data, the classification criteria are not met.***Skin corrosion/irritation** *Based on available data, the classification criteria are not met.***Serious eye damage/irritation** *Based on available data, the classification criteria are not met.***Respiratory or skin sensitisation** *Based on available data, the classification criteria are not met.***Germ cell mutagenicity** *Based on available data, the classification criteria are not met.***Carcinogenicity** *Based on available data, the classification criteria are not met.***Reproductive toxicity** *Based on available data, the classification criteria are not met.***STOT-single exposure** *Based on available data, the classification criteria are not met.***STOT-repeated exposure** *Based on available data, the classification criteria are not met.***Aspiration hazard** *Based on available data, the classification criteria are not met.***11.2 Information on other hazards****Endocrine disrupting properties***None of the ingredients is listed.***SECTION 12: Ecological information****12.1 Toxicity****Aquatic toxicity:** *No further relevant information available.***12.2 Persistence and degradability** *No further relevant information available.***12.3 Bioaccumulative potential** *No further relevant information available.***12.4 Mobility in soil** *No further relevant information available.*

(Contd. on page 5)

Trade name: Kalibrierlösung CLY11-D 12,64 mS

(Contd. of page 4)

**12.5 Results of PBT and vPvB assessment**PBT: *Not applicable.*vPvB: *Not applicable.***12.6 Endocrine disrupting properties***The product does not contain substances with endocrine disrupting properties.***12.7 Other adverse effects****Additional ecological information:****General notes:** *Not hazardous for water.***SECTION 13: Disposal considerations****13.1 Waste treatment methods****Recommendation** *Smaller quantities can be disposed of with household waste.***European waste catalogue**16 05 09 | *discarded chemicals other than those mentioned in 16 05 06, 16 05 07 or 16 05 08***Uncleaned packaging:****Recommendation:** *Disposal must be made according to official regulations.***Recommended cleansing agents:** *Water, if necessary together with cleansing agents.***SECTION 14: Transport information****14.1 UN number or ID number**

ADR, ADN, IMDG, IATA

Void

**14.2 UN proper shipping name**

ADR, ADN, IMDG, IATA

Void

**14.3 Transport hazard class(es)**

ADR, ADN, IMDG, IATA

Class

Void

**14.4 Packing group**

ADR, IMDG, IATA

Void

**14.5 Environmental hazards:****Marine pollutant:**

No

**14.6 Special precautions for user***Not applicable.***14.7 Maritime transport in bulk according to IMO instruments***Not applicable.***Transport/Additional information:***Not dangerous according to the above specifications.***UN "Model Regulation":**

Void

**SECTION 15: Regulatory information****15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****Labelling according to Regulation (EC) No 1272/2008** *Void***Hazard pictograms** *Void***Signal word** *Void***Hazard statements** *Void***Directive 2012/18/EU****Named dangerous substances - ANNEX I** *None of the ingredients is listed.***DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II***None of the ingredients is listed.*

(Contd. on page 6)

Trade name: Kalibrierlösung CLY11-D 12,64 mS

(Contd. of page 5)

**REGULATION (EU) 2019/1148****Annex I - RESTRICTED EXPLOSIVES PRECURSORS (Upper limit value for the purpose of licensing under Article 5(3))***None of the ingredients is listed.***Annex II - REPORTABLE EXPLOSIVES PRECURSORS***None of the ingredients is listed.***Regulation (EC) No 273/2004 on drug precursors***None of the ingredients is listed.***Regulation (EC) No 111/2005 laying down rules for the monitoring of trade between the Community and third countries in drug precursors***None of the ingredients is listed.***15.2 Chemical safety assessment:** *A Chemical Safety Assessment has not been carried out.***SECTION 16: Other information***This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.***16.3 Recommended restriction of use****Department issuing SDS:** PCC-TWR**Contact:** MSDS.pcc@endress.com**Date of previous version:** 12.05.2021**Version number of previous version:** 3**Abbreviations and acronyms:***RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)**IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)**ICAO: International Civil Aviation Organisation**ICAO-TI: Technical Instructions by the "International Civil Aviation Organisation" (ICAO)**ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)**IMDG: International Maritime Code for Dangerous Goods**IATA: International Air Transport Association**GHS: Globally Harmonised System of Classification and Labelling of Chemicals**EINECS: European Inventory of Existing Commercial Chemical Substances**ELINCS: European List of Notified Chemical Substances**CAS: Chemical Abstracts Service (division of the American Chemical Society)**PBT: Persistent, Bioaccumulative and Toxic**vPvB: very Persistent and very Bioaccumulative***\* Data compared to the previous version altered.**