


DO NOT SCALE DRAWING

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	DRAWN	08-08-2013	



Part No.	A
TRDLCBST-1-01	1.6
TRDLCBST-2-01	3.2
TRDLCBST-3-01	4.8
TRDLCBST-4-01	6.4
TRDLCBST-5-01	7.9
TRDLCBST-6-01	9.5
TRDLCBST-7-01	11.1
TRDLCBST-8-01	12.7
TRDLCBST-9-01	14.3
TRDLCBST-10-01	15.9
TRDLCBST-14-01	22.2

Notes:

- 1.RoHS Compliant;
- 2.Top Hole:Ø2.54±0.05mm;
Panel Thickness:1.63mm;
- 3.Bottom Hole:Ø2.54±0.05mm;
Panel Thickness:1.63mm;



DESIGN RIGHT. TR FASTENINGS LTD. 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED.
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS.
SURFACE FINISH:
TOLERANCES:
L≤4 = ±0.1 4<L≤15 = ±0.2
15<L≤50 = ±0.3 50<L≤100 = ±0.4

NAME	DATE
DRAWN MARTIN ELLIOTT	08/08/2013
CHK'D	
APP'VD	

CUSTOMER PART NO.

MATERIAL

PA66 UL94 V2

HEAT TREATMENT

N/A

FINISH

NATURAL

TITLE

MINI SUPPORT POST

DWG NO.

TRDLCBST-X-01

A3

PROJECTION



SHEET 1 OF 1