



Figure similar

POWER SUPPLY; PHASES:1; PN(KW):0,12;
 UPRI(V):400-230+/-15; USEC(V DC):24; ISEC(A DC):5/6 (60/40 CEL); F(HZ):50...60; VECTOR GR./SHIELD WNG.:II0 /0; PROTECTION CL.:I; TA/ISOKL:60 /B; W(%):5; IP00; TYPE OF TERMINALS:SCREW/TAB CONNECTION; INSTALLATION:MOUNTING RAILS; EN 61558-2-6, EN61131-2 >SAFETY ISOLATING TRANSFORMER<

General technical data:

| | | |
|--|--|----------------------------------|
| Product designation | | 4AV2200-2EB00-0B |
| product brand name | | SIDAC |
| Vector group | | Ii0 |
| Certificate of suitability | | CE |
| Product function | | |
| <ul style="list-style-type: none"> • Temperature monitoring | | No |
| <ul style="list-style-type: none"> • Insulation monitoring | | No |
| <ul style="list-style-type: none"> • Short-circuit and overload proof | | No |
| <ul style="list-style-type: none"> • varistor protective wiring | | Yes |
| Operating resource protection class | | I |
| Number of shielding windings | | 0 |

Inputs:

| | | |
|--|----|-----|
| Phase number of the inputs | | 1 |
| Type of current of the inputs | | AC |
| Input voltage | | |
| <ul style="list-style-type: none"> • _1 Rated value | V | 415 |
| <ul style="list-style-type: none"> • _2 Rated value | V | 400 |
| <ul style="list-style-type: none"> • _3 Rated value | V | 385 |
| <ul style="list-style-type: none"> • _4 Rated value | V | 245 |
| <ul style="list-style-type: none"> • _5 Rated value | V | 230 |
| <ul style="list-style-type: none"> • _6 Rated value | V | 215 |
| Electrical input frequency | | |
| <ul style="list-style-type: none"> • minimum | Hz | 50 |

| | | |
|--|----|--------------------------------------|
| • maximum | Hz | 60 |
| Input voltage | | |
| • minimum | V | 193.5 |
| • maximum | V | 439.9 |
| Input current | | |
| • _1 Rated value | A | 0.57 |
| • _2 Rated value | A | 0.58 |
| • _3 Rated value | A | 0.59 |
| • _4 Rated value | A | 0.95 |
| • _5 Rated value | A | 1 |
| • _6 Rated value | A | 1.05 |
| Type of electrical connection at input for main current circuit | | screw-type terminals / tab terminals |

| | | |
|---|---|--------------------------------------|
| Outputs: | | |
| Type of current | | DC |
| • _1 at output | | |
| Output voltage | | |
| • _1 Rated value | V | 24 |
| Output voltage of the measurement signal at analog output for DC maximum | V | 28.8 |
| Output voltage of the measurement signal at analog output for DC minimum | V | 20.4 |
| Output current | | |
| • _1 Rated value | A | 5 |
| Type of electrical connection at output for main current circuit | | screw-type terminals / tab terminals |
| Relative residual ripple | | |
| • of the output voltage 1 for main current circuit maximum | % | 5 |

| | | |
|--|----|------|
| Ambient conditions: | | |
| Thermal class acc. to IEC 60085 | | B |
| Ambient temperature Rated value | °C | 60 |
| Protection class IP | | IP00 |

| | | |
|---|---|---------------|
| Mechanical data: | | |
| Mounting type | | standard rail |
| Construction form of the iron core | | EI 105/60 |
| Width | m | 105 |
| Height | m | 157 |
| Depth | m | 113 |

| | | |
|---------------------------------|--|--|
| Certificates/ approvals: | | |
|---------------------------------|--|--|



[Declaration of
Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4AV22002EB000B>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AV22002EB000B>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=4AV22002EB000B&lang=en

last modified:

16.03.2015