

## Manual vacuum lifter with 2 suction heads

Carrying capacity 60 kg

### Application:

For the safe and secure lifting, carrying and holding of discs, sheets and panels.

### Execution:

- Bell-shaped vacuum lifter
- 2 suction discs

### Advantage:

- One-handed operation possible
- For rapid and efficient working procedures



<b>Art. no.</b>	<b>77178 045</b>
<b>Brand</b>	BOHLE
<b>Manufacturer Part Number</b>	BO 602 50
<b>Load-carrying capacity</b>	60 kg
<b>Direction of force</b>	Perpendicular
<b>Material</b>	Aluminium
<b>Number of suction heads</b>	2 PCS
<b>Suction head diameter</b>	130 mm
<b>Number of pieces in assortment/set</b>	1 PCS
<b>Gross Weight</b>	1.098 kg
<b>Product Group</b>	7EM

### EAN

4010122066514