





NOTES:

1. MATERIALS AND FINISHES:
 BODY - BRASS, NICKEL PLATING
 BAYONET - ZINC DIECAST, NICKEL PLATING
 CONTACT - BRASS, GOLD PLATING
 INSULATOR - DELRIN
2. ELECTRICAL:
 A. IMPEDANCE: 50 OHM
 B. FREQUENCY RANGE: DC 0-4 GHz
 C. VSWR(RETURN LOSS): 1.5 (14 dB), MAX.
 D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
 A. DURABILITY: 500 CYCLES MIN.
 B. TEMPERATURE RANGE: - 65°C to +165°C
4. CRIMPED FERRULE
 HEX. CRIMP SIZE .215"
5. CRIMPED CONTACT PIN
 HEX. CRIMP SIZE .068"

31-335 RFX		REVISIONS			
PART NO	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ	⊕ ⊕ ⊕	BAYONET WAS BRASS	7/13/06	4&154	GH



RECOMMENDED
CABLE STRIPPING DIM'S



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
 0.5 - 6mm ±0.1mm
 6 - 30mm ±0.2mm
 30 - 120mm ±0.3mm
 ANGLES ±1°

NOTICE - These drawings, specifications or other data (i) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp. or to any other person, to anyone for any purpose is not to be regarded by implication or otherwise in any manner, licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL	DRAWN CARRA	DATE 23-Jun-06	TITLE BNC R/A CRIMP PLUG	Amphenol RF Sunnyvale USA, Taiwan, Shenzhen China www.amphenolrf.com	
REFERENCE	ENGINEER	DATE 23-Jul-06	SCALE: 3/1	SHEET 2 OF 2	DRAWING NO. 31122B1-ND3G-58U-50
FINISH	APPROVED <i>R. Coltrane</i>	DATE 7/13/06	DWG SIZE D	CODE ID 7486R	ITEM NO. 011122AAF58ND5F
	CAD FILE F:\DWG\BAY\22B1\58U-50\ND3G5Z		REV D		PART NO. 31-335-RFX