


## Data Sheet

**Type Number** ..... 344  
**Designation IEC** ..... SR 42  
**System** ..... Silver oxide / Zinc /  
 NaOH - Electrolyte



**Nominal Voltage** ..... 1,55 V  
**Typical Capacity C** ..... 100 mAh  
 Load 5,6 kOhm, at 20°C down to 1.2 V

**Weight (approx.)** ..... 1,49 g  
**Volume** ..... 0,38 ccm  
**Coding**..... Date of Manufacturing  
 Month/Year

**Temperature Ranges** min max.  
 Storage ..... -10°C 65°C  
 Discharge ..... -10°C 65°C

**Dimensions** min max.  
 Diameter (Ø)..... 11,25 11,6  
 Height (A/B) ..... 3,3 3,6

**Segment** ..... Watch

**Main Applications** ..... Watch  
 Photo  
 Electronic

### Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous	5600 Ω	Time:	365
24h/d, 7d/w		Capacity [mAh]:	100
Current [μA]:	275	Energy [mWh]:	155