

Table scales FOB



Application:

Suitable for the increased hygienic requirements in medical environments

Execution:

- Stainless steel design of housing and weighing tray, thus rust-resistant and easy to clean thanks to smooth surfaces
- Supports you in your HACCP-compliant quality system
- Dust and splash water protection IP67 (only in battery operation)
- High mobility: Thanks to battery operation and compact, lightweight construction, suitable for use in multiple locations (kitchen, sales room, canteen, food laboratory etc.)
- Dual range scales automatically switch to the next largest weighing range [Max] and readability [d]
- with a large weighing range and degree of protection IP67

Delivery:

with battery (4 x 1.5 V AA) and work protection hood



Art. no.	49000 038
Brand	KERN
Manufacturer Part Number	FOB 7K-4NL
Type description	FOB 7K-4NL
Max. weight measuring range	7500 g
Digit increment, weight	0.5 g
Digit height	25 mm
Plate size	200 x 252 mm
Material of cover panel	Stainless steel
With unit counting	No
Reproducibility	0.5 g
Reproducibility 2	1 g
Linearity	1.5 g
Linearity 2	3 g
Settling time scale	2 s
Display type	LCD
Housing dimensions (LxWxH)	285 x 255 x 90 mm
Gross Weight	4.495 kg
Product Group	447

EAN

4045761161566