

electric chain hoist basic/DC-Com, 2-stage

load capacity: 125-2000 kg

DEMAG

Application:

The performance spectrum of the chain block is tailored to with applications involving normal loads—just right for everyday use. It therefore meets the high quality standards of a DEMAG product.

Execution:

- Plug and lift—all chain block electric connections are plug-in
- With a hinged, universal suspension bracket, the tension can simply be suspended in the wheel set
- The length of the control cable can be adjusted without any additional wiring effort
- Fatigue-free operation due to ergonomically optimised and robust control switch DSC
- Fast change of the entire chain drive without dismantling the motor or transmission parts
- Protection control 24 V, type of protection IP 55
- Operating hour meter
- Operation limit switch for top-most/bottom-most hook position

Advantage:

- Service room
- Infrared diagnostic interface
- Speed-monitored brake/sliding clutch operating principle

Delivery:

Upon request: Manual and electric trolleys, see illustration. Larger hook paths and higher load stroke up to 5000 kg.



Art. no.	77099 012
Brand	DEMAG
Manufacturer Part Number	93130246
Load-carrying capacity	125 kg
Lift height	4 m
Stroke speed control	In two steps
Stroke speed of precision hoist	2 m/min
Stroke speed of main hoist	8 m/min
Number of load chains	1 PCS
Construction height	364 mm
Length	422 mm
Depth	268 mm
Model	DC-Com 1-125 V8/2
FEM group	3 m
Colour	Azure blue RAL 5009
Gross Weight	22.000 kg
Product Group	774