



GE  
Lighting



Single Ended Halogen - HPL  
HPL 575W LL 240V

**88475**

## Product information

HPL lamps were developed using GE Six Sigma process, these lamps encompass modern halogen technology and high production standards. HPL optical system for superior field smoothness and cosine distribution- Integral heat sink base reduces seal temperature, increases durability and maximises life- Shock resistant filament array and patented gas chemistry minimises arc-out risk during alignment and focusing.



## Product data

EAN Code	0043168884754
DUN Code	10043168884751
Bulb Shape	Tubular
Bulb Diameter [mm]	19
Cap/Base	Special
Gross weight per piece [g]	73
Maximum Overall Length [mm]	106
Net weight per piece [g]	54
Brand	General Electric (GE)

## Performance data

Nominal power [W]	575
Nominal lamp voltage [V]	240
Nominal lumens [lm]	11800
Nominal correlated colour temperature (CCT) [K]	3000
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	1500
Ballast Required	No
Coil type	6C-8
Energy efficiency class (EEC)	D
Light Center Length [mm]	60.3
Weighted energy consumption [kWh/1000h]	591.13

## Logistic data

Pack Quantity	12
Pallet quantity EUR (PC)	3276
Pallet quantity UK (PC)	4116
Outer case size	175 x 135 x 138 (mm)
Layer quantity	468 EUR, 588 UK
Layer quantity EUR	468
Layer quantity UK	588
Product status	Available

## Application areas



Theatre

## Downloads & Links

[Go to the catalog site \(HTTP\)](#)[Entertainment Solution Spectrum Catalogue \(PDF\)](#)[Lighting design tools & calculators \(HTTP\)](#)

## Disclaimer

Special Purpose Lamp, Not suited for household illumination