

HMI EVENT 575 W

HMI EVENT | Metal halide lamps, single-ended



Areas of application

- Trade fairs or exhibitions of cars, boats, industrial plants and motorcycles

Product benefits

- Extremely uniform light distribution, reduced color or brightness shifts
- Constant daylight color temperature throughout the entire lamp lifetime
- High light output
- Very good color rendering index of $R_a > 90$ throughout the whole lamp lifetime
- Minimal light scattering
- Optimized filling



Product datasheet

Technical data


Electrical data

Nominal wattage	575.00 W
Nominal current	76.9 A
Nominal voltage	95.0 V

Photometrical data

Nominal luminous flux	49000 lm
Color temperature	6000 K

Dimensions & weight



Length	145.0 mm
Diameter	30.0 mm

Additional product data

Base (standard designation)	G22
-----------------------------	-----

Product datasheet

Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation, HMI lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. Information on safety and handling is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899301726	HMI EVENT 575 W	Folding carton box 1	46 mm x 46 mm x 143 mm	0.30 dm ³	153.00 g
4052899301733	HMI EVENT 575 W	Shipping carton box 10	245 mm x 105 mm x 165 mm	4.24 dm ³	1600.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
