



## **CBH25L50-V6 Cable Cleat Bracket, CBH Series, 316L SS, 0.79-0.98in H, 0-1.97in W**

### CBH25L50-V6

The CBH25L50-V6 Mounting Cleat Bracket is an effective option for protecting against high short circuit fault current requirements in harsh environments. This product eliminates the need for drilling holes through rungs to secure cable cleats and utilizes an easy-to-use swing bolt assembly. Designed for use with Panduit's CCSSTR Series Stainless Steel Trefoil Cleats and CCALTR Series Aluminum Trefoil Cleats. Features 25mm height, 50mm length, and 316L stainless steel.

### Specifications

Note	For 50mm rung width and 25mm rung height when used with CCSSTR (22mm rung height when used with CCALTR)
Product Type	Cable Cleat Bracket
Color	Natural
Environment	Indoor and Outdoor
For Use With	Stainless Steel Trefoil Cable Cleats
Material	316 Stainless Steel
Maximum Installation Temperature (°C)	60
Maximum Installation Temperature (°F)	140
Minimum Installation Temperature (°C)	-40
Minimum Installation Temperature (°F)	-40
Maximum Operating Temperature (°C)	60
Maximum Operating Temperature (°F)	140
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Resistance Properties	Flame-Resistant

### Packaging Detail

UPC	61305644989
Std. Pkg. Qty.	5
Std. Pkg. Volume (cf)	0.0730
Std. Ctn. Qty.	25
Std. Ctn. Volume (cf)	0.3650